

**CA 100 C****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Orders on request only



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

**General ordering data**

Version	Automatic stripper and crimper
Order No.	<a href="#">1266370000</a>
Type	CA 100 C
GTIN (EAN)	4050118056303
Qty.	1 items

## CA 100 C

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	280 mm	Depth (inches)	11.0236 inch
Height	390 mm	Height (inches)	15.3543 inch
Width	410 mm	Width (inches)	16.1417 inch
Net weight	23000 g		

## Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1

## PW65 maintenance - automatic stripping/crimping

Stripping range	0.14 - 0.34 mm <sup>2</sup> (~AWG 26 - 22)	Drive	Electropneumatic
Pulse time	approx. 1.5 s	Wire end ferrules cross-section, max.	0.34 mm <sup>2</sup>
Wire end ferrules cross-section, min.	0.14 mm <sup>2</sup>	Crimping length	6/8 mm
Consumables	loose cable lugs, With and without plastic collar	Length of wire-end ferrule	10/12 mm
Compressed-air connection	5 bar	Electrical connection	100-240 V / 50/65 Hz

## Classifications

ETIM 8.0	EC002778	ETIM 9.0	EC002778
ETIM 10.0	EC002778	ECLASS 14.0	17-13-01-01
ECLASS 15.0	17-13-01-01		

**Drawings**

