

VG 21 HQ EMV68 9-13**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

The increasing sensitivity of electronic components and the increasing electromagnetic interference frequencies require cable glands to play an important role in the shielding concept of a system. This type of EMC cable glands are made for shielding against interference frequencies, with a 360° screening connection. A Finger-locking seal provides superior cable retention & strain relief, next to it, the cable gland meets the mechanical requirements of EN 62444. Due to the patented design a very easy and fast assembly will be possible.

General ordering data

Version	Heavy-duty connectors, Accessories, Cable glands, Brass, nickel-plated
Order No.	1273900000
Type	VG 21 HQ EMV68 9-13
GTIN (EAN)	4050118063516
Qty.	1 items

VG 21 HQ EMV68 9-13

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Net weight	39.6 g
------------	--------

Temperatures

Limit temperature	-40 °C ... 130 °C
-------------------	-------------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	b5ff1f66-ddba-4739-9fc0-0521ddb52139

General information

Outer cable diameter, max.	13 mm	Outer cable diameter, min.	9 mm
Halogen	halogen-free	AF size 1	27 mm
AF size	27 mm	Protection degree	IP68
Cable gland	PG 21	Basic material	Brass, nickel-plated
External thread	PG 21		

Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-01
ECLASS 15.0	27-14-08-01		