

ETA 1180 01 0.4A**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



As accessories for our wide product portfolio of fuse terminal blocks, we also offer the appropriate fuse links. The portfolio includes device protection fuses (miniature fuses) from 5x20 mm up to 10x38 mm, E 14 to E 18 fuse links, as well as automotive fuses and automatic circuit breakers. Gauge rings for the fuse holders round off the overall portfolio.

General ordering data

| | |
|------------|----------------------------|
| Version | Miniature fuse, 0.4 A |
| Order No. | 1278880000 |
| Type | ETA 1180 01 0.4A |
| GTIN (EAN) | 4050118091380 |
| Qty. | 5 items |

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 52.3 mm | Depth (inches) | 2.0591 inch |
| Height | 24.4 mm | Height (inches) | 0.9606 inch |
| Width | 8.2 mm | Width (inches) | 0.3228 inch |
| Net weight | 10.3 g | | |

Temperatures

| | |
|---------------------|---------------|
| Ambient temperature | -5 °C...40 °C |
|---------------------|---------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------|
| RoHS Compliance Status | Compliant |
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| | |
|--------|-------|
| Colour | black |
|--------|-------|

System specifications

| | |
|---------|----------------|
| Version | Fuse cartridge |
|---------|----------------|

Additional technical data

| | | | |
|---------------------|-----------------|------------------|---------|
| Installation advice | Direct mounting | Type of mounting | Plugged |
|---------------------|-----------------|------------------|---------|

General

| | |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

Rating data

| | | | |
|---------------|------|-----------------|-------|
| Rated voltage | 64 V | Nominal current | 0.4 A |
|---------------|------|-----------------|-------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002704 | ETIM 9.0 | EC002704 |
| ETIM 10.0 | EC002704 | ECLASS 14.0 | 27-14-20-01 |
| ECLASS 15.0 | 27-14-20-01 | | |