

**SAIL-M12W-8-3.0U****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration.

Our developers have focused specifically on this issue and designed a host of different M8 and M12 sensor-actuator cables so you are bound to find the solution you need for your application.

Is there something you have not managed to find or you feel needs explanation? Talk to us!

**General ordering data**

|            |                                                                                                                                                    |
|------------|----------------------------------------------------------------------------------------------------------------------------------------------------|
| Version    | Sensor/actuator line, One end without connector, M12, Number of poles : 8, 3 m, pin, 90°, Shielded: No, LED: No, Sheath material: PUR, Halogen: No |
| Order No.  | <a href="#">1279420300</a>                                                                                                                         |
| Type       | SAIL-M12W-8-3.0U                                                                                                                                   |
| GTIN (EAN) | 4050118076455                                                                                                                                      |
| Qty.       | 1 items                                                                                                                                            |

## SAIL-M12W-8-3.0U

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E307231

## Dimensions and weights

Net weight 129.36 g

## Environmental Product Compliance

RoHS Compliance Status Compliant with exemption

RoHS Exemption (if applicable/known) 6c

REACH SVHC Lead 7439-92-1

SCIP e8d8af70-4c85-4483-bc8c-9bc5b598e2a9

## Technical specifications for cable

|                                                |                                  |                                      |                                                    |
|------------------------------------------------|----------------------------------|--------------------------------------|----------------------------------------------------|
| Cable length                                   | 3 m                              | Sheathing colour                     | black                                              |
| Suitable for cable carriers                    | Yes                              | Core cross-section                   | 0.25 mm <sup>2</sup>                               |
| Number of wires                                | 8                                | Shielded                             | No                                                 |
| Halogen                                        | No                               | Insulation                           | PP                                                 |
| Acceleration                                   | 5 m/s <sup>2</sup>               | Bending radius, min., moving         | 10 x cable diameter                                |
| Bending radius, min., stationary               | 5 x cable diameter               | Bending cycles                       | 1 mill.                                            |
| Resistance to spread of flame                  | in accordance with IEC 60332-2-2 | Speed                                | 5 m/s                                              |
| Sheath material                                | PUR                              | Cable length configurable            | No                                                 |
| Outer cladding in accordance with UL AWM style | 20549 (80 °C / 300 V)            | Core in accordance with UL AWM style | 10493 (80 °C / 300 V)                              |
| Type is hybrid cable                           | No                               | Irradiation crosslinked              | No                                                 |
| Welding spark resistance                       | No                               | Colour coding                        | white, brown, green, yellow, grey, pink, blue, red |
| Torsion resistance                             | 180 °/m                          | Temperature range, stationary        | -40...90 °C                                        |
| Resistant to welding beads                     | No                               | Temperature range, moving            | -30...90 °C                                        |
| Number of poles                                | 8                                | Outside diameter                     | 5.9 mm ± 0.2 mm                                    |

## General technical data

|                              |              |                        |                                   |
|------------------------------|--------------|------------------------|-----------------------------------|
| Coding                       | A-coded      | Connection thread      | M12                               |
| Contact surface              | Gold-plated  | LED                    | No                                |
| Version                      | pin, 90°     | Housing main material  | TPU                               |
| Insulation resistance        | ≥ 108 Ω      | Contact material       | CuZn                              |
| Nominal voltage              | 30 V         | Nominal current        | 2 A                               |
| AF size                      | 13 mm        | Protection degree      | IP65, IP67, IP68, when screwed in |
| Plugging cycles              | ≥ 100        | Pollution severity     | 3                                 |
| jumpered                     | No           | Threaded ring material | Brass, nickel-plated              |
| Temperature range of housing | -25...+85 °C | Tightening torque      | M12: 1.0 Nm                       |

**SAIL-M12W-8-3.0U****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)
**Technical data****Electrical properties**

|                       |                                |                 |      |
|-----------------------|--------------------------------|-----------------|------|
| Insulation resistance | $\geq 108 \Omega$              | Nominal voltage | 30 V |
| Rated current         | 2 A (8-pole) / 1.5 A (12-pole) |                 |      |

**General standards**

|                    |                 |                         |         |
|--------------------|-----------------|-------------------------|---------|
| Connector standard | IEC 61076-2-101 | Certificate no. (cULus) | E307231 |
|--------------------|-----------------|-------------------------|---------|

**Standards**

|                    |                 |
|--------------------|-----------------|
| Connector standard | IEC 61076-2-101 |
|--------------------|-----------------|

**Plug, left**

|           |                                                                             |
|-----------|-----------------------------------------------------------------------------|
| Plug left | M12, A-coded, Number of poles: 8, male contact, angled 0°, plug, unshielded |
|-----------|-----------------------------------------------------------------------------|

**Plug, right**


|            |                    |
|------------|--------------------|
| Plug right | Free conductor end |
|------------|--------------------|

**Classifications**


|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001855    | ETIM 9.0    | EC001855    |
| ETIM 10.0   | EC001855    | ECLASS 14.0 | 27-06-03-11 |
| ECLASS 15.0 | 27-06-03-11 |             |             |

## Drawings


### Dimensioned drawing



### Pole scheme



### Wiring diagram



### The ideal tool: Screwty® with torque function

Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F

