

## SAIL-M12GM12G-8S30U

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration.

Our developers have focused specifically on this issue and designed a host of different M8 and M12 sensor-actuator cables so you are bound to find the solution you need for your application.

Our sensor cables come with 360° shielding which provides protection against electromagnetic interference.

Is there something you have not managed to find or you feel needs explanation? Talk to us!

### General ordering data

|            |  |
|------------|--|
| Version    | Sensor/actuator line, Connecting line, M12 / M12, Number of poles : 8, 30 m, pin, straight - socket, straight, Shielded: Yes, LED: No, Sheath material: PUR, Halogen: No |
| Order No.  | <a href="#">1279463000</a>   |
| Type       | SAIL-M12GM12G-8S30U  |
| GTIN (EAN) | 4050118623437  |
| Qty.       | 1 items  |

**SAIL-M12GM12G-8S30U****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Approvals**

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E307231

**Dimensions and weights**

Net weight 1735 g

**Environmental Product Compliance**

RoHS Compliance Status Compliant

REACH SVHC Lead 7439-92-1

SCIP e8d8af70-4c85-4483-bc8c-9bc5b598e2a9

**Technical specifications for cable**

|  |                       |                                  |  |
|--|-----------------------|----------------------------------|--|
| Cable length                                   | 30 m                  | Sheathing colour                 | black  |
| Suitable for cable carriers                    | Yes                   | Core cross-section               | 0.25 mm <sup>2</sup>                               |
| Shielded                                       | Yes                   | Halogen                          | No   |
| Insulation                                     | PP                    | Acceleration                     | 5 m/s <sup>2</sup>                                 |
| Bending radius, min., moving                   | 12 x cable diameter   | Bending radius, min., stationary | 5 x cable diameter                                 |
| Bending cycles                                 | 1 mill.               | Speed                            | 100 m/s  |
| Sheath material                                | PUR                   | Configurable cable length        | No   |
| Outer cladding in accordance with UL AWM style | 20549 (80 °C / 300 V) | Irradiation crosslinked          | No   |
| Welding spark resistance                       | No                    | Colour coding                    | blue, red, white, brown, green, yellow, grey, pink |
| Torsion resistance                             | 360 °/m               | Temperature range, stationary    | -40...80 °C  |
| Resistant to welding beads                     | No                    | Temperature range, moving        | -25...80 °C  |
| Number of poles                                | 8                     | Outside diameter                 | 6.3 mm ± 0.2 mm                                    |

**General technical data**

|                        |                                   |                              |                |
|------------------------|-----------------------------------|------------------------------|----------------|
| Coding                 | A-coded                           | Connection thread            | M12 / M12      |
| Contact surface        | Gold-plated                       | LED                          | No             |
| Version                | pin, straight - socket, straight  | Housing main material        | PUR            |
| Insulation resistance  | 108 Ω                             | Nominal voltage              | 30 V           |
| Nominal current        | 2 A                               | AF size                      | 13 mm          |
| Protection degree      | IP67, when screwed in, IP65, IP66 | Plugging cycles              | ≥ 100          |
| Pollution severity     | 3                                 | jumpered                     | No             |
| Threaded ring material | Brass, nickel-plated              | Temperature range of housing | -40 ... +85 °C |
| Tightening torque      | M12: 1.0 Nm                       |                              |                |

**Electrical properties**

|                       |       |                 |      |
|-----------------------|-------|-----------------|------|
| Insulation resistance | 108 Ω | Nominal voltage | 30 V |
|-----------------------|-------|-----------------|------|

**SAIL-M12GM12G-8S30U**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

**General standards**

Certificate no. (cULus) E307231

**Plug, left**

Plug left M12, A-coded, IP67, male contact, straight, Plastic, shielded

**Plug, right**

Plug right M12, A-coded, IP67, female contact, straight, Plastic, shielded

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001855    | ETIM 9.0    | EC001855    |
| ETIM 10.0   | EC001855    | ECLASS 14.0 | 27-06-03-11 |
| ECLASS 15.0 | 27-06-03-11 |             |             |


SAIL-M12GM12G-8S30U

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany


www.weidmueller.com

Drawings

Dimensioned drawing




Dimensioned drawing




Straight socket

Pole scheme



Male

Pole scheme



Socket

## SAIL-M12GM12G-8S30U


**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

# Drawings

[www.weidmueller.com](http://www.weidmueller.com)

### Wiring diagram

### The ideal tool: Screwty® with torque function



Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F