

IE-SW-PL10MT-3GT-7TX
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com
Product image


Weidmüller's Premium Line consists of high-end switches with advanced management and security features. It is suitable for demanding network solutions. The equipment can be delivered with Fast Ethernet or Gigabit Ethernet ports. With their advanced ring redundancy technology (recovery time ≤ 20 ms), these devices raise the reliability and availability of your industrial networks. The optional SFP transceiver can be fitted offering a high degree of flexibility. Gigabit versions permit use in networks with a high volume of communications

- Managed Fast Ethernet versions in a high-quality metal housing (IP 30)
- Versions with 10 or 18 ports and Gigabit uplink ports
- Full Gigabit switch with 9 ports
- Supports all standard TCP/IP-based protocols in industrial networks (for example Ethernet/IP, Modbus/TCP)
- Integrated redundancy mechanisms (recovery time ≤ 20 ms) increase the reliability in network ring structures
- Approvals: CE, FCC, cULus, Class I Div. 2 / ATEX, DNV / GL

General ordering data

Version	Network switch, managed, Fast/Gigabit Ethernet, Number of ports: 3 * RJ45 10/100/1000BaseT(X), 7 * RJ45 10/100BaseT(X), IP30, -40 °C...75 °C
Order No.	1286930000
Type	IE-SW-PL10MT-3GT-7TX
GTIN (EAN)	4050118077902
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Last order date	2025-11-29T00:00:00+01:00
Alternative product	IE-SW-AL14M-12GT-2GESEFP

IE-SW-PL10MT-3GT-7TX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E230683
Certificate no. (cULusEX)	E223527

Dimensions and weights

Depth	107 mm	Depth (inches)	4.2126 inch
Height	135 mm	Height (inches)	5.3149 inch
Width	80.2 mm	Width (inches)	3.1575 inch
Net weight	1170 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...75 °C
Humidity	5 to 95 % (non-condensing)		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	9229992a-00b9-4096-8962-200a7f33e289

EMC conformity and approvals

Explosive risk zone	UL/cUL, Class I, Division 2, Groups A, B, C and D, ATEX Zone 2 Ex nA nC IIC T4 Gc	Free fall	According to IEC 60068-2-32
EMC standards	EN 55032, EN 55024, CISPR 32, FCC Part 15 Subpart B Class A, IEC 61000-4-2 ESD: Contact: 6 kV; Air: 8 kV, IEC 61000-4-3 RS: 80 MHz to 1 GHz: 20 V/m, IEC 61000-4-4 EFT: Power: 2 kV; Signal: 2 kV, IEC 61000-4-5 Surge: Power: 2 kV; Signal: 2 kV, IEC 61000-4-6 CS: 10 V, EN 61000-4-8	Vibration	according to IEC 60068-2-6
Shock	according to IEC 60068-2-27	Safety standard	UL508, UL 60950-1, EN 60950-1

Environmental conditions

Operating temperature, max.	75 °C	Operating temperature, min.	-40 °C
Humidity	5 to 95 % (non-condensing)	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

IE-SW-PL10MT-3GT-7TX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Guarantee

Time interval 5 years

Interfaces

RJ45 ports	10/100BaseT(X), 10/100/1000BaseT(X), auto negotiation	Console port interface	RS-232
Function DIP switch	Turbo-Ring, Master, Coupler, Reserve	Alarm contact	2 relay outputs with a current capacity of 1 A at 24 V DC
Number of ports	3 * RJ45 10/100/1000BaseT(X), 7 * RJ45 10/100BaseT(X)	Digital inputs	2 inputs with the same ground, isolated • +13 To +30 V for logic "1" • -30 To +3 V for logic "0" • Max. input current: 8 mA
LED indicator	PWR1, PWR2, FAULT, 10/100M (TP-Port), 1000M (Gigabit-Port), MSTR/HEAD, CPLR/TAIL		

MTBF

MTBF	According to Standard	Telcordia (Bellcore), GB
	Operating time (hours), min.	911314 h

Management features

Device configuration	Webbrowser (HTTP/ HTTPS), SNMP v1/v2c/v3, Telnet console, Local serial console port (RS-232 via RJ-45 port), Windows tool	Monitoring function	SNMP v1/v2c/v3, Link Layer Discovery Protocol (LLDP), Port mirroring, Port statistics, Port monitoring, Syslog, RMON (Remote monitoring), Event based warning via E-Mail, Event based warning via relay, Event based warning via SNMP trap
Network redundancy	Spanning Tree Protocol (STP), Rapid Spanning Tree Protocol (RSTP), Turbo-Ring (recovery time <20/50 ms at Fast/ Gigabit Ethernet interface), Turbo-Chain (recovery time <20/50 ms at Fast/ Gigabit Ethernet interface), Link Aggregation Control Protocol (LACP)	Network traffic filter	Quality of Service (QoS), Tag based VLAN, Port based VLAN, IGMP v1/ v2, GMRP, Traffic Rate Limiting
IP-address management	Static, BootP, RARP, DHCP- Client, DHCP-Server (port based), DHCP Option 82 (Relay Agent)	Security functions	VLAN segmentation, Enable/disable ports, Access control (port based via IEEE 802.1X), Access control list (MAC-based), Loop protection, TACACS + and IEEE 802.1X User Authentication
Time synchronization management	SNTP client, NTP client, PTPv1	Industrial protocol support	PROFINET device acc. to conformance class B, EtherNet/IP, Modbus/TCP slave

IE-SW-PL10MT-3GT-7TX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Power supply

Reverse polarity protection	Available		
Supply voltage	24 V DC, 2 redundant inputs		
Overload current protection	Existing		
Connection type	2 removable 6-pin terminal blocks		
Voltage supply range	Voltage type	DC	
	Voltage, min.	12 V	
	Voltage, max.	45 V	
Current consumption	Voltage	24 V	
	Current	0.65 A	

Switch characteristics

Priority queues	4	Max. number of available VLANs	64
VLAN-ID min	1	VLAN-ID max	4094
IGMP-Groups	256	MAC table size	8 K
Packet buffer size	1 Mbit	Bandwidth backplane	7.4 Gbit/s

Technical data

Housing main material	metal	Type of mounting	DIN rail, Panel (with optional mounting kit)
Protection degree	IP30	Speed	Fast/Gigabit Ethernet
Switch	managed		

Technology

MIB	MIB-II, Ethernet-Like MIB, P-BRIDGE MIB, Q-BRIDGE MIB, Bridge MIB, RSTP MIB, RMON MIB Group 1, 2, 3, 9	Data switching	Store and Forward
Flow control	IEEE 802.3x flow control, Back pressure flow control	Standard	IEEE 802.3 for 10BaseT, IEEE 802.3u for 100BaseT(X), IEEE 802.3ab for 1000BaseT(X), IEEE 802.3x for flow control, IEEE 802.1D-2004 for the Spanning Tree protocol, IEEE 802.1w for Rapid STP, IEEE 802.1Q for VLAN tagging, IEEE 802.1p for Class of Service, IEEE 802.1X for authentication, IEEE 802.3ad for port trunk with LACP

Classifications

ETIM 8.0	EC000734	ETIM 9.0	EC000734
ETIM 10.0	EC000734	ECLASS 14.0	19-17-04-01
ECLASS 15.0	19-17-04-01		