

SAIL-7/8G-3-5.0U

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration.

The 7/8" cables tend to be used for power supply applications.

Is there something you have not managed to find or you feel needs explanation? Talk to us!

General ordering data

| | |
|------------|---|
| Version | Sensor/actuator line, One end without connector, 7/8", Number of poles : 3 (2 + PE), 5 m, pin, straight, Shielded: No, LED: No, Sheath material: PUR, Halogen: No |
| Order No. | 1292080500 |
| Type | SAIL-7/8G-3-5.0U |
| GTIN (EAN) | 4050118087826 |
| Qty. | 1 items |

SAIL-7/8G-3-5.0U

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|-------------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E307231 |

Dimensions and weights

| | |
|------------|-------|
| Net weight | 250 g |
|------------|-------|

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | e8d8af70-4c85-4483-bc8c-9bc5b598e2a9 |

Technical specifications for cable

| | | | |
|--|------------------------|-------------------------------|---------------------------|
| Cable length | 5 m | Sheathing colour | black |
| PE function | Yes | Suitable for cable carriers | Yes |
| Core cross-section | 1.5 mm ² | Shielded | No |
| Halogen | No | Insulation | TPM |
| Bending radius, min., moving | 7.5 x cable diameter | Bending cycles | 5 Mio |
| Sheath material | PUR | Configurable cable length | No |
| Outer cladding in accordance with UL AWM style | 20234 (80 °C / 1000 V) | Irradiation crosslinked | No |
| Welding spark resistance | No | Colour coding | blue, brown, Green/yellow |
| Torsion resistance | 0 °/m | Temperature range, stationary | -50...80 °C |
| Resistant to welding beads | No | Temperature range, moving | -20...80 °C |
| Number of poles | 3 (2 + PE) | Outside diameter | 7.4 mm ± 0.2 mm |

General technical data

| | | | |
|------------------------|-----------------------|------------------------------|----------------|
| Coding | none | Connection thread | 7/8" |
| Contact surface | Au (Gold) | LED | No |
| Version | pin, straight | Housing main material | PUR |
| Insulation resistance | 108 Ω | Contact material | CuZn |
| Nominal voltage | 300 V | Nominal current | 12 A |
| Protection degree | IP68, when screwed in | Plugging cycles | ≥ 100 |
| Pollution severity | 3 | jumped | No |
| Rated impulse voltage | 2500 V | Rated voltage (UL) | 600 V |
| Threaded ring material | Diecast zinc | Temperature range of housing | -40 ... +85 °C |

Electrical properties

| | | | |
|-----------------------|------------------------------------|-----------------|-------|
| Insulation resistance | 108 Ω | Nominal voltage | 300 V |
| Rated current | 9 A (4- and 5-pole), 12 A (3-pole) | | |

General standards

| | |
|-------------------------|---------|
| Certificate no. (cULus) | E307231 |
|-------------------------|---------|

SAIL-7/8G-3-5.0U

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Plug, left**

| | |
|-----------|---|
| Plug left | IP68, male contact, straight, Plastic, unshielded |
|-----------|---|

Plug, right

| | |
|------------|--------------------|
| Plug right | free conductor end |
|------------|--------------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001855 | ETIM 9.0 | EC001855 |
| ETIM 10.0 | EC001855 | ECLASS 14.0 | 27-06-03-11 |
| ECLASS 15.0 | 27-06-03-11 | | |

SAIL-7/8G-3-5.0U

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing



Male, straight

Pole scheme



Male

Wiring diagram



The ideal tool: Screwty® with torque function

Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F

