

SAIL-7/8BG-5-18U

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration.

The 7/8" cables tend to be used for power supply applications.

Is there something you have not managed to find or you feel needs explanation? Talk to us!

General ordering data

| | |
|---------------------|--|
| Version | Sensor/actuator line, 7/8", Number of poles : 5 (4 + PE), 18 m, Shielded: No, LED: No, Sheath material: PUR, Halogen: No |
| Order No. | 1292191800 |
| Type | SAIL-7/8BG-5-18U |
| GTIN (EAN) | 4050118626629 |
| Qty. | 1 items |
| Delivery status | This article will no longer be available in the future. |
| Last order date | 2026-09-30T00:00:00+02:00 |
| Alternative product | SAIL-7/8BG-5-15U |

SAIL-7/8BG-5-18U

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Net weight 1000 g

Environmental Product Compliance

RoHS Compliance Status Compliant with exemption

RoHS Exemption (if applicable/known) 6c

REACH SVHC Lead 7439-92-1

SCIP e8d8af70-4c85-4483-bc8c-9bc5b598e2a9

Technical specifications for cable

| | | | |
|--|------------------------|-------------------------------|---|
| Cable length | 18 m | Sheathing colour | black |
| PE function | Yes | Suitable for cable carriers | Yes |
| Core cross-section | 1.5 mm ² | Shielded | No |
| Halogen | No | Insulation | TPM |
| Bending radius, min., moving | 7.5 x cable diameter | Bending cycles | 5 Mio |
| Sheath material | PUR | Configurable cable length | No |
| Outer cladding in accordance with UL AWM style | 20234 (80 °C / 1000 V) | Irradiation crosslinked | No |
| Welding spark resistance | No | Colour coding | brown, white, blue, black, Green/yellow |
| Torsion resistance | 0 °/m | Temperature range, stationary | -50...80 °C |
| Resistant to welding beads | No | Temperature range, moving | -20...80 °C |
| Number of poles | 5 (4 + PE) | Outside diameter | 8.7 mm ± 0.2 mm |

General technical data

| | | | |
|------------------------------|----------------|------------------------|-----------------------|
| Coding | none | Connection thread | 7/8" |
| Contact surface | Au (Gold) | LED | No |
| Housing main material | PUR | Insulation resistance | 108 Ω |
| Contact material | CuZn | Nominal voltage | 300 V |
| Nominal current | 9 A | Protection degree | IP68, when screwed in |
| Plugging cycles | ≥ 100 | Pollution severity | 3 |
| jumpered | No | Rated impulse voltage | 2500 V |
| Rated voltage (UL) | 600 V | Threaded ring material | Diecast zinc |
| Temperature range of housing | -40 ... +85 °C | | |

Electrical properties

| | | | |
|-------------------|-------|-----------------------|-------|
| Volume resistance | ≤3 mΩ | Insulation resistance | 108 Ω |
| Nominal voltage | 300 V | | |

Plug, left

Plug left 7/8", IP68, female contact, straight, Plastic, unshielded

SAIL-7/8BG-5-18U

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Plug, right

| | |
|------------|--------------------|
| Plug right | free conductor end |
|------------|--------------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001855 | ETIM 9.0 | EC001855 |
| ETIM 10.0 | EC001855 | ECLASS 14.0 | 27-06-03-11 |
| ECLASS 15.0 | 27-06-03-11 | | |

SAIL-7/8BG-5-18U

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Drawings

Dimensioned drawing



Straight socket

Pole scheme



Socket

Wiring diagram



The ideal tool: Screwty® with torque function

Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F

