

## SAIE-7/8S-5-0.2-PG11

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

### General ordering data

Version	Built-in plugs, 7/8", pin, straight, Mounting thread: PG 11, Number of poles: 5, Strand / cable length: 0.2 m
Order No.	<a href="#">1292470000</a>
Type	SAIE-7/8S-5-0.2-PG11
GTIN (EAN)	4050118088526
Qty.	1 items

## SAIE-7/8S-5-0.2-PG11

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate No. (cURus)	E307231

### Dimensions and weights

Net weight	45.18 g
------------	---------

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	7baf363e-d867-435e-844e-c01f32ebf146

### Technical specifications for cable

Core cross-section	0.75 mm <sup>2</sup>	Strand / cable length	0.2 m
Colour coding	black, blue, Green/yellow, brown, white	Number of poles	5

### Technical data customisable plug-in connectors

Number of poles	5	Coding	none
Contact surface	Gold-plated	Type of connection	Pin
Housing main material	Zinc diecast, nickel-plated	Contact material	CuZn
Nominal voltage	300 V	Nominal current	8 A
Protection degree	IP67, when screwed in	Plugging cycles	≥ 100
Cable gland	PG 11	Rated current	8 A (4- and 5-pole), 10 A (3-pole)
Temperature range of housing	-25...+85 °C		

### General data

Number of poles	5
Coding	none
Connection thread	7/8"
Contact surface	Gold-plated
Tightening torque	1.5 Nm
Core cross-section	0.75 mm <sup>2</sup>
Type of connection	Pin
Housing main material	Zinc diecast, nickel-plated
Contact material	CuZn
Nominal voltage	300 V
Nominal current	8 A
Protection degree	IP67, when screwed in
Plugging cycles	≥ 100
Cable gland	PG 11
Basic material	PUR/ PUR
Rated voltage	300 V
Rated current	8 A (4- and 5-pole), 10 A (3-pole)
Connection 1	7/8"

**SAIE-7/8S-5-0.2-PG11**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

Connection 2	Flying wires		
Strand / cable length	0.2 m		
Rated impulse voltage	4000 V		
Mounting thread	PG 11		
Mounting torque range	6 ... 6.25 Nm		
Rated voltage (UL)	600 V		
Mounting torque	min.	6 Nm	
	max.	6.25 Nm	
Temperature range of housing	-25...+85 °C		
Conductor O.D.	-		

**Classifications**

ETIM 8.0	EC003570	ETIM 9.0	EC003570
ETIM 10.0	EC003570	ECLASS 14.0	27-44-01-03
ECLASS 15.0	27-44-01-03		



SAIE-7/8S-5-0.2-PG11

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany


www.weidmueller.com

Drawings

Wiring diagram



Pole scheme



## SAIE-7/8S-5-0.2-PG11

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Accessories

## Brass lock nuts, nickel-plated



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

## General ordering data

Type	SKMU PG 11-MS	Version	
Order No.	<a href="#">1694090000</a>	SKMU MS (brass locknut), Locknut, PG 11, 3 mm, Brass, nickel-plated	
GTIN (EAN)	4008190872250		
Qty.	100 ST		