

IE-C5DB4RE0100MSAXXX-E

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

| | |
|------------|--|
| Version | System cable, M12 D-code – IP 67 angled socket, Open, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), Radox GWK S, 10 m |
| Order No. | 1309810100 |
| Type | IE-C5DB4RE0100MSAXXX-E |
| GTIN (EAN) | 4050118148152 |
| Qty. | 1 items |

IE-C5DB4RE0100MSAXXX-E

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|-------|-----------------|---------------|
| Length | 10 m | Length (inches) | 393.7008 inch |
| Net weight | 794 g | | |

Temperatures

| | | | |
|--------------------------|----------------|-----------------------|----------------|
| Storage temperature | -40 °C...90 °C | Operating temperature | -40 °C...90 °C |
| Installation temperature | -25 °C...90 °C | | |

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 67cf1078-beca-4687-860b-dc475a6ec24a |

Cable specific standards

| | | | |
|---|--|--|--|
| Fire protection in buses | According to ISO 6722-1 5.22 (UN ECE-R 118.01) | Fluorine content | According to EN 60684-2 Section 45.2 |
| Flames propagate vertically on bundled cables | According to BS4066-3, DIN EN 50266-2-5, According to IEC 60332-3-25 D | Multi-wire metallic data and control cable | According to EN50288-2-2 |
| Hydrogen halide content | According to EN-50267-2-1, According to IEC 60754-1 | Corrosiveness of fumes | to IEC 60754-2 |
| Fire safety for railway vehicles | According to DIN 5510-2 fire safety levels 1,2,3,4, According to BS 6853, According to EN50288-2-2, According to EN 45545, HL1 - HL3 | Impervious to smoke | According to BS 6853 Appendix D, in accordance with EN 50268-2, According to IEC 61034-2 |
| Poisonous gases | According to BS 6853 Appendix B | | |

Cable structure

| | | | |
|--------------------------|---|-----------------------|---------------|
| Strands | 7 | Sheathing colour | black, SF/UTP |
| Cross-section | 2*2*AWG 22/7 - 2*2*0.36 mm ² | Shielding | SF/UTP |
| Insulation cross-section | 1.95 mm | Sheath diameter, max. | 7.55 mm |
| Sheath diameter, min. | 6.95 mm | Material sheath | Radox GKW S |

Electrical properties of cable

| | |
|----------|---|
| Category | Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B) |
|----------|---|

Mechanical and material properties of cable

| | | | |
|---------------------------------|-------------------------------|---------------------|--|
| Resistance to oils | in accordance with EN 50306-3 | Halogen | halogen-free, according to IEC 60754-2 |
| Min. bending radius, repetitive | 6 *diameter | Abrasion resistance | very good |

IE-C5DB4RE0100MSAXXX-E

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

| | | | |
|-------------------------------|--|------------------------|----------------|
| Resistance to spread of flame | in accordance with IEC 60332-1-2 | Corrosiveness of fumes | to IEC 60754-2 |
| Impervious to smoke | According to BS 6853 Appendix D, in accordance with EN 50268-2, According to IEC 61034-2 | | |

Plug

| | | | |
|------------|--------------------|-----------|--|
| Plug right | free conductor end | Plug left | M12, D-coded, IP67, female contact, angled 90°, plug, Zinc diecast, shielded |
|------------|--------------------|-----------|--|

Plug, left

| | |
|-----------|--|
| Plug left | M12, D-coded, IP67, female contact, angled 90°, plug, Zinc diecast, shielded |
|-----------|--|

Plug, right

| | |
|------------|--------------------|
| Plug right | free conductor end |
|------------|--------------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002599 | ETIM 9.0 | EC002599 |
| ETIM 10.0 | EC002599 | ECLASS 14.0 | 27-06-03-08 |
| ECLASS 15.0 | 27-06-03-08 | | |