

## RSM-16DI 24VDC Z

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Digital input interface with opto module or relay isolation for electrical signal transmission between the PLC and the field.

- Electrical isolation by pluggable relays.
- Integrated LED status display.

### General ordering data

Version	Interface, RSM, Optos, LED
Order No.	<a href="#">1312010000</a>
Type	RSM-16DI 24VDC Z
GTIN (EAN)	4050118114454
Qty.	1 items

## RSM-16DI 24VDC Z

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

Depth	72 mm	Depth (inches)	2.8346 inch
Height	109 mm	Height (inches)	4.2913 inch
Width	124 mm	Width (inches)	4.8819 inch
Net weight	343.24 g		

### Temperatures

Storage temperature	-20...70 °C	Operating temperature	-20...50 °C
---------------------	-------------	-----------------------	-------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	71d9bdc4-a0b5-4af0-93bd-2ad4e523fb14

### General data

LED status display per relay	green	LED status of the supply voltage	yellow
Power supply fuse	2 A		

### Connection data

Number of poles (control side)	20-pole plug	Wiring system	1-wire
Connection on control side	Plug-in connector in acc. with IEC60603-13 / DIN41651		

### Rating data

Mechanical service life	5 x 10 <sup>6</sup> switching cycles
-------------------------	--------------------------------------

### Ratings data input

Input voltage	24 V DC ± 10%	Input current	13 mA
---------------	---------------	---------------	-------

### Ratings data output

Relay type	RSS	Material of contacts	AgNi gold flashed
Rated voltage	24 V DC ± 10%	Max. DC continuous current	0.1 A
Minimum contact current	1 mA	Minimum contact voltage	1 V

### Insulation coordinates (EN50178)

Rated input insulation voltage	≤ 50 V DC	Rated output insulation voltage	≤ 50 V DC
Overvoltage category input/input	III	Overvoltage category input/output	III

## RSM-16DI 24VDC Z

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

Pollution severity level	2	Pulse voltage test (1,2/50µs)	1.5 kV
Insulation test voltage AC	0.35 kV	Clearance input/output	≥ 6 mm

### Connection field

Type of connection	Tension-clamp connection	Clamping range, max.	2.5 mm <sup>2</sup>
Clamping range, min.	0.13 mm <sup>2</sup>		

### Supply connection

Type of connection	Tension-clamp connection	Clamping range, min.	0.13 mm <sup>2</sup>
Clamping range, max.	2.5 mm <sup>2</sup>		

### Classifications

ETIM 8.0	EC002780	ETIM 9.0	EC002780
ETIM 10.0	EC002780	ECLASS 14.0	27-14-11-52
ECLASS 15.0	27-14-11-52		

**RSM-16DI 24VDC Z**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

