

STB 36.8/IH/RT WTL6/1**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Current and voltage transformer wiring

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

General ordering data

Version	Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm
Order No.	1312540000
Type	STB 36.8/IH/RT WTL6/1
GTIN (EAN)	4050118180992
Qty.	50 items
Delivery status	This article will no longer be available in the future.
Last order date	2027-04-30T00:00:00+02:00

STB 36.8/IH/RT WTL6/1

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	39.8 mm	Depth (inches)	1.5669 inch
Height	36.8 mm	Height (inches)	1.4488 inch
Width	6 mm	Width (inches)	0.2362 inch
Diameter	6 mm	Net weight	4.93 g

Temperatures

Ambient temperature	-50 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	dce63e23-eea1-4eaa-9071-1c98fc8fa2ea

Material data

Basic material	Polyamide 66	Colour	red
UL 94 flammability rating	V-2		

System specifications

Version	For the terminals
---------	-------------------

Additional technical data

Installation advice	Direct mounting	Type of mounting	when screwed in
---------------------	-----------------	------------------	-----------------

Dimensions

Diameter	6 mm	Plug-in depth	11.1 mm
----------	------	---------------	---------

General

Installation advice	Direct mounting	Operating temperature range, max.	100 °C
---------------------	-----------------	-----------------------------------	--------

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		