


SFR 2/21 MC NE WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The SlimFix Redesign SFR is a modification of the familiar SlimFix conductor marker which significantly simplifies installation. The marker is simply slid onto the cable and is securely fixed in no time.

General ordering data

| | |
|------------|--|
| Version | SlimFix R, Conductor and cable markers, 2.2 - 2.9 mm, 21 x 5.8 mm, white |
| Order No. | 1318730000 |
| Type | SFR 2/21 MC NE WS |
| GTIN (EAN) | 4050118124521 |
| Qty. | 400 items |

SFR 2/21 MC NE WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Height | 21 mm | Height (inches) | 0.8268 inch |
| Width | 5.8 mm | Width (inches) | 0.2283 inch |
| Net weight | 0.25 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

Environmental Product Compliance

| | | | |
|--------------------------|-----------------------------|------------------|--|
| RoHS Compliance Status | Compliant without exemption | | |
| REACH SVHC | No SVHC above 0.1 wt% | | |
| Product Carbon Footprint | Cradle to gate | 0.002 kg CO2 eq. | |

General data

| | | | |
|--------------------------------------|---|-----------|--|
| Width | 5.8 mm | | |
| UL 94 flammability rating | V-2 | | |
| Operating temperature range, max. | 100 °C | | |
| Operating temperature range, min. | -40 °C | | |
| Colour | white | | |
| Halogen | No | | |
| Basic material | Polyamide 66 | | |
| Printed characters | neutral | | |
| Number of markers per packaging unit | Form of supply | MultiCard | |
| Size of labelling field | 21 x 3.2 mm | | |
| Recommended industries | Transportation, Machinery | | |
| compatible printer | PRINTJET CONNECT , MCP BASIC 2 , MCP PLUS 2 | | |
| Number of markers per combination | 1 MultiCard = Conductor and cable markers | | |
| Operating temperature range | -40...100 °C | | |

Conductor and cable markers

| | | | |
|----------------------------------|----------------------------|-------------------------------|---------------------|
| Halogen | No | Conductor cross-section, max. | 1.5 mm ² |
| Conductor cross-section, min. | 0.75 mm ² | Conductor O.D., max. | 2.9 mm |
| Conductor O.D., min. | 2.2 mm | Conductor O.D. | 2.2 - 2.9 mm |
| Cross-section for connected wire | 0.75 - 1.5 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |

Drawings

