


**SFR 3/21 MC NE WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The SlimFix Redesign SFR is a modification of the familiar SlimFix conductor marker which significantly simplifies installation. The marker is simply slid onto the cable and is securely fixed in no time.

**General ordering data**

Version	SlimFix R, Conductor and cable markers, 3 - 3.7 mm, 21 x 5.8 mm, white
Order No.	<a href="#">1318750000</a>
Type	SFR 3/21 MC NE WS
GTIN (EAN)	4050118124514
Qty.	256 items

## SFR 3/21 MC NE WS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Height	21 mm	Height (inches)	0.8268 inch
Width	5.8 mm	Width (inches)	0.2283 inch
Net weight	0.32 g		

### Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.003 kg CO2 eq.	

### General data

Width	5.8 mm		
UL 94 flammability rating	V-2		
Operating temperature range, max.	100 °C		
Operating temperature range, min.	-40 °C		
Colour	white		
Halogen	No		
Basic material	Polyamide 66		
Printed characters	neutral		
Number of markers per packaging unit	Form of supply	MultiCard	
Size of labelling field	21 x 4.6 mm		
Recommended industries	Transportation, Machinery		
compatible printer	<a href="#">PRINTJET CONNECT</a> , <a href="#">MCP BASIC 2</a> , <a href="#">MCP PLUS 2</a>		
Number of markers per combination	1 MultiCard = Conductor and cable markers		
Operating temperature range	-40...100 °C		

### Conductor and cable markers

Halogen	No	Conductor cross-section, max.	2.5 mm <sup>2</sup>
Conductor cross-section, min.	1.5 mm <sup>2</sup>	Conductor O.D., max.	3.7 mm
Conductor O.D., min.	3 mm	Conductor O.D.	3 - 3.7 mm
Cross-section for connected wire	1.5 - 2.5 mm <sup>2</sup>		

### Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

**Drawings**

