

SM 42/42-30 K MC NE WS


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



SM is a MultiCard marker for labelling control and signalling devices. The tags are clipped into the carriers or attached by means of the adhesive film already fitted to them. Customised tags can be created with the PrintJet CONNECT or Plotter marking systems.

- Users can quickly produce tags to suit their needs
- No need to stock expensive standard tags
- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- For extreme demands, we recommend the ETO SM protective film
- Holders can be used for the 22-mm or 30-mm-diameter push-buttons from Siemens, ABB, Moeller and Télémécanique

For custom printing: Please send us a file of our labelling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	SwitchMark, Device markers, 42 x 42 mm, for cam switches, Type T0, white
Order No.	1323530000
Type	SM 42/42-30 K MC NE WS
GTIN (EAN)	4050118126693
Qty.	20 items

SM 42/42-30 K MC NE WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	1.2 mm	Depth (inches)	0.0472 inch
Height	42 mm	Height (inches)	1.6535 inch
Width	42 mm	Width (inches)	1.6535 inch
Diameter	30 mm	Net weight	3.48 g

Temperatures

Operating temperature range	-40...60 °C
-----------------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.048 kg CO2 eq.	

General data

Material colour according to resistance code	9		
Version	Self-adhesive		
Width	42 mm		
UL 94 flammability rating	V-2		
Operating temperature range, max.	60 °C		
Operating temperature range, min.	-40 °C		
Colour	white		
Halogen	No		
Basic material	Polyamide 66		
Printed characters	without		
Number of markers per packaging unit compatible printer	Form of supply	MultiCard	
	PRINTJET CONNECT, MCP BASIC 2, MCP PLUS 2		
Number of markers per combination	1 MultiCard = Device markers		
Operating temperature range	-40...60 °C		
Application/manufacturer	for cam switches, Type T0		

Device markers

Diameter	30 mm	Halogen	No
----------	-------	---------	----

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

Drawings

