

TM-I 12/18 MC SDR

Weidmüller Interface GmbH & Co. KG

Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



TM-I is an acknowledged and accredited marker type for traffic engineering applications. There are various different tag lengths available for individual labelling with long character strings. Easy handling of separation and installation thanks to the project marker field. Pre-attachment of sleeves and retrofitting of tags offer excellent versatility. The special contour of TM-I allows easy assembly and secures firm positioning. They are compatible with a number of commercially available sleeves. Thanks to the MultiCard format, the tags can be printed quickly and conveniently with the PrintJet CONNECT, plotter or the STI pen.

- Easy handling of separation and installation thanks to the project marker field.
- Acknowledged and accredited marker for traffic engineering applications
- Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
- Not suited for labelling with P-Ink or STI pen in connection with CLI T sleeves

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	TM-I, Insert markers, 1.7 - 79 mm, 30 x 4 mm, To customer specification
Order No.	1323720000
Type	TM-I 12/18 MC SDR
GTIN (EAN)	4050118126792
Qty.	48 items

TM-I 12/18 MC SDR

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

RoHS	Conform
------	---------

Dimensions and weights

Height	30 mm	Height (inches)	1.1811 inch
Width	4 mm	Width (inches)	0.1575 inch
Net weight	0.29 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%
Product Carbon Footprint	Cradle to gate 0.003 kg CO2 eq.

General data

Orientation of print	horizontal and vertical				
Number per sheet	80				
Type of printing	To customer specification				
Width	4 mm				
UL 94 flammability rating	V-2				
Operating temperature range, max.	100 °C				
Operating temperature range, min.	-40 °C				
Colour	To customer specification				
Halogen	No				
Basic material	Polyamide 66				
Printed characters	Requires M-Print PRO File				
Advice label	Colour based on customer requirements (Please send M-Print PRO file)				
Number of markers per packaging unit	Form of supply	MultiCard			
compatible printer	PRINTJET CONNECT , MCP BASIC 2 , MCP PLUS 2				
Number of markers per combination	1 MultiCard = Insert markers				
Operating temperature range	-40...100 °C				

Conductor and cable markers

Halogen	No	Conductor O.D., max.	79 mm
Conductor O.D., min.	1.7 mm	Conductor O.D.	1.7 - 79 mm

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		