

## SM DIA 60-22 K MC NE GE


**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



SM is a MultiCard marker for labelling control and signalling devices. The tags are clipped into the carriers or attached by means of the adhesive film already fitted to them. Customised tags can be created with the PrintJet CONNECT or Plotter marking systems.

- Users can quickly produce tags to suit their needs
- No need to stock expensive standard tags
- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- For extreme demands, we recommend the ETO SM protective film
- Holders can be used for the 22-mm or 30-mm-diameter push-buttons from Siemens, ABB, Moeller and Télémécanique

For custom printing: Please send us a file of our labelling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

Version	SwitchMark, Device markers, 60 x 60 mm, ø 60 - 22 mm, Siemens 3 SB, Eaton Moeller M22-PV, yellow
Order No.	<a href="#">1323750000</a>
Type	SM DIA 60-22 K MC NE GE
GTIN (EAN)	4050118127010
Qty.	10 items

## SM DIA 60-22 K MC NE GE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	1.2 mm	Depth (inches)	0.0472 inch
Height	60 mm	Height (inches)	2.3622 inch
Width	60 mm	Width (inches)	2.3622 inch
Diameter	22 mm	Net weight	9.06 g

### Temperatures

Operating temperature range	-40...60 °C
-----------------------------	-------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption	
REACH SVHC	No SVHC above 0.1 wt%	
Product Carbon Footprint	Cradle to gate	0.101 kg CO2 eq.

### General data

Version	Self-adhesive	
Width	60 mm	
UL 94 flammability rating	V-2	
Operating temperature range, max.	60 °C	
Operating temperature range, min.	-40 °C	
Colour	yellow	
Halogen	No	
Basic material	Polyamide 66	
Printed characters	without	
Number of markers per packaging unit	Form of supply	MultiCard
compatible printer	<a href="#">PRINTJET CONNECT</a> , <a href="#">MCP BASIC 2</a> , <a href="#">MCP PLUS 2</a>	
Number of markers per combination	1 MultiCard = Device markers	
Operating temperature range	-40...60 °C	
Application/manufacturer	ø 60 - 22 mm, Siemens 3 SB, Eaton Moeller M22-PV	

### Device markers

Diameter	22 mm	Halogen	No
----------	-------	---------	----

### Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

**Drawings**

