

IE-PS-M12X-P-FH**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems. The IDC is simple and quick to assemble since this technology allows the conductor to be inserted directly into the terminal point, without crimping or having to strip the insulation. It also has excellent functional security.

General ordering data

| | |
|------------|---|
| Version | Plugs prefabricated to customer spec., M12, IDC, Cat.6A / Class EA (ISO/IEC 11801 2010), IP67 plugged |
| Order No. | 1324020000 |
| Type | IE-PS-M12X-P-FH |
| GTIN (EAN) | 4050118127782 |
| Qty. | 10 items |

IE-PS-M12X-P-FH

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|-------------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E316369 |

Dimensions and weights

| | | | |
|----------|---------|------------|---------|
| Diameter | 16.8 mm | Net weight | 33.95 g |
|----------|---------|------------|---------|

Temperatures

| | | |
|--------------------------|-----------------------|----------------|
| Storage temperature | Operating temperature | -40 °C...85 °C |
| Installation temperature | | |

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 67cf1078-beca-4687-860b-dc475a6ec24a |

Technical data customisable plug-in connectors

| | | | |
|-------------------------------|------------------------------------|-------------------------------|--|
| Number of poles | 8 | Coding | X-coded |
| Contact surface | Gold-plated | LED | No |
| Type of connection | Insulation displacement connection | Housing main material | Zinc diecast |
| Insulation resistance | 100 MΩ | Cable diameter, max. | 9.7 mm |
| Cable diameter, min. | 5 mm | Category | Cat.6A / Class EA (ISO/IEC 11801 2010) |
| Contact material | Brass | Conductor cross-section, max. | 0.34 mm ² |
| Conductor cross-section, min. | 0.14 mm ² | Nominal voltage | 48 V |
| Nominal current | 0.5 A | Protection degree | IP67 plugged |
| Plugging cycles | ≥ 100 | Pollution severity | 2 |
| Gender of contact | Male | Shield connection | Yes, screwed |
| Threaded ring material | Zinc diecast, tin plated | | |

General Info

| | | | |
|--|---------------------|--|--|
| Number of poles | 8 | Connection 1 | M12 |
| Connection 2 | IDC | Wiring | EIA/TIA T568 A, EIA/TIA T568 B |
| UL 94 flammability rating | V-0 | Housing main material | Zinc diecast |
| Insulation cross-section, max. | 1.6 mm | Category | Cat.6A / Class EA (ISO/IEC 11801 2010) |
| Connection thread | M12 | Contact material | Brass |
| Contact surface | Gold-plated | Wire connection diameter, solid, min. | 0.41 mm |
| Connection diameter, solid | 0.41...0.64 mm | Wire connection diameter, solid, max. | 0.64 mm |
| Conductor connection cross-section, solid (AWG) | AWG 26/1...AWG 22/1 | Wire cross-section, solid, min. (AWG) | AWG 26/1 |
| Connection diameter, flexible | 0.48...0.76 mm | Wire cross-section, solid, max. (AWG) | AWG 22/1 |
| Conductor connection cross-section, flexible (AWG) | AWG 26/7...AWG 22/7 | Wire connection diameter, flexible, min. | 0.48 mm |

Creation date 09.03.2026 02:54:20 MEZ

Catalogue status / Drawings

IE-PS-M12X-P-FH

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

| | | | |
|---|--------------------------|--|----------------------|
| Wire connection diameter, flexible, max. | 0.76 mm | Wire connection cross section, finely stranded, max. | 0.32 mm ² |
| Wire cross-section, solid, min. | 0.34 mm ² | Wire cross-section, solid, max. | 0.32 mm ² |
| Conductor connection cross-section, flexible | ...0.32 mm ² | Wire cross-section, finely stranded, min. (AWG) | AWG 26/7 |
| Wire cross-section, finely stranded, max. (AWG) | AWG 22/7 | Sheath diameter, min. | 5 mm |
| Sheath diameter, max. | 9.7 mm | Contact holder materials | PA |
| Shielding | 360° all-round enclosure | Protection degree | IP67 plugged |
| Plugging cycles | ≥ 100 | | |

Electrical properties

| | | | |
|-----------------------|----------------------------|-----------------|------|
| Insulation resistance | 100 MΩ | Nominal voltage | 48 V |
| PoE / PoE+ | conforming to IEEE 802.3at | | |

General standards

| | | | |
|--------------------|-----------------|-------------------------|---------|
| Connector standard | IEC 61076-2-109 | Certificate no. (cULus) | E316369 |
|--------------------|-----------------|-------------------------|---------|

Standards


| | | | |
|--------------------|-----------------|----------------------------------|----------------|
| Connector standard | IEC 61076-2-109 | Fire safety for railway vehicles | DIN EN 45545-2 |
|--------------------|-----------------|----------------------------------|----------------|

Classifications


| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002635 | ETIM 9.0 | EC002635 |
| ETIM 10.0 | EC002635 | ECLASS 14.0 | 27-44-01-16 |
| ECLASS 15.0 | 27-44-01-16 | | |

Drawings

Dimensioned drawing



Pinning



IE-PS-M12X-P-FH

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Screwty® cable gland tool



The ideal tool for any application
 Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

General ordering data

| | | | |
|------------|----------------------------|---------|---|
| Type | SCREWTY SET | Version | |
| Order No. | 1910000000 | | Cable gland tool for M8, M12 lines and connectors |
| GTIN (EAN) | 4032248436842 | | |
| Qty. | 1 ST | | |

Screwty® cable gland tool with torque function



The ideal tool for any application
 Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

General ordering data

| | | | |
|------------|----------------------------|---------|---|
| Type | SCREWTY SET -DM | Version | |
| Order No. | 1920000000 | | Cable gland tool for M8, M12 lines and connectors |
| GTIN (EAN) | 4032248436859 | | |
| Qty. | 1 ST | | |

IE-PS-M12X-P-FH

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Screwty® cable gland tool



The ideal tool for any application
 Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

General ordering data

| | | | |
|------------|----------------------------|---------|-------------------------------------|
| Type | SCREWTY- M12 F | Version | |
| Order No. | 1900020000 | | Cable gland tool for M12 connectors |
| GTIN (EAN) | 4032248375851 | | |
| Qty. | 1 ST | | |

Screwty® cable gland tool with torque function



The ideal tool for any application
 Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

General ordering data

| | | | |
|------------|----------------------------|---------|-------------------------------------|
| Type | SCREWTY-M12 F-DM | Version | |
| Order No. | 1900021000 | | Cable gland tool for M12 connectors |
| GTIN (EAN) | 4032248436828 | | |
| Qty. | 1 ST | | |