

IE-FM6C2UE0250MSD1SD1X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Assembled IE cables, FO breakout cable, multimode, SC duplex - SC duplex, black, Core diameter 62.5 µm

General ordering data

Version	Dragline cable, SC IP 67 bayonet V01 metal, SC IP 67 bayonet V01 metal, 62.5 µm, PUR, 250 m
Order No.	1318012500
Type	IE-FM6C2UE0250MSD1SD1X
GTIN (EAN)	4050118123975
Qty.	1 items

IE-FM6C2UE0250MSD1SD1X

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Length	250 m	Length (inches)	9842.5 197 inch
Net weight	15800 g		

Temperatures

Storage temperature	-55 °C...85 °C	Operating temperature	-40 °C...85 °C
Installation temperature	-55 °C...60 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

Fibre-optic

Fibre type	GOF, Multimode, OM1	Attenuation	2.7 dB/km at 850 nm, ≤ 0.5 dB/km at 1300 nm
Insertion loss	≤ 0.4 dB	Return loss (attenuation)	≥ 30 dB
Bandwidth	200 MHz*km at 850 nm, 500 MHz*km at 1300 nm		

Cable structure

Sheath diameter	7.5–8 mm	Sheathing colour	black
Material sheath	PUR	Cable layout	Break-out dragline
Primary coating	245.00 µm	Core diameter	62.5 µm

Mechanical and material properties of cable

Halogen	No	Min. bending radius, repetitive	70 mm
Min. bending radius, once only	25 mm	Bending cycles	100,000

Plug

Plug right	SC, IP67, male contact, straight, V1 Bayonett, plug, Zinc diecast, unshielded	Plug left	SC, IP67, male contact, straight, V1 Bayonett, plug, Zinc diecast, unshielded
------------	---	-----------	---

Plug, left

Plug left	SC, IP67, male contact, straight, V1 Bayonett, plug, Zinc diecast, unshielded
-----------	---

Plug, right

Plug right	SC, IP67, male contact, straight, V1 Bayonett, plug, Zinc diecast, unshielded
------------	---

IE-FM6C2UE0250MSD1SD1X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold


Germany

www.weidmueller.com**Technical data****Classifications**

ETIM 8.0	EC002607	ETIM 9.0	EC002607
ETIM 10.0	EC002607	ECLASS 14.0	27-06-10-03
ECLASS 15.0	27-06-10-03		

Drawings

Detailed drawing




IE-FM6C2UE0250MSD1SD1X

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

V0 material



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

General ordering data

Type	VT SF 5/21 MC NE WS V0	Version
Order No.	1689470001	SlimFix, Conductor and cable markers, 4.8 - 7.4 mm, 21 x 7.4 mm,
GTIN (EAN)	4008190872571	white
Qty.	160 ST	
Type	VT SF 6/21 MC NE WS V0	Version
Order No.	1730560001	SlimFix, Conductor and cable markers, 5.8 - 7.8 mm, 21 x 8.4 mm,
GTIN (EAN)	4008190954611	white
Qty.	160 ST	