


## SFR 2/12 MC SDR

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



The SlimFix Redesign SFR is a modification of the familiar SlimFix conductor marker which significantly simplifies installation. The marker is simply slid onto the cable and is securely fixed in no time.

### General ordering data

Version	SlimFix R, Conductor and cable markers, 2.2 - 2.9 mm, 12 x 5.8 mm, To customer specification
Order No.	<a href="#">1318780000</a>
Type	SFR 2/12 MC SDR
GTIN (EAN)	4050118179583
Qty.	80 items

## SFR 2/12 MC SDR

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Height	12 mm	Height (inches)	0.4724 inch
Width	5.8 mm	Width (inches)	0.2283 inch
Net weight	0.17 g		

## Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.002 kg CO2 eq.	

## General data

Number per sheet	80		
Type of printing	To customer specification		
Width	5.8 mm		
UL 94 flammability rating	V-2		
Operating temperature range, max.	100 °C		
Operating temperature range, min.	-40 °C		
Colour	To customer specification		
Halogen	No		
Basic material	Polyamide 66		
Printed characters	Requires M-Print PRO File		
Advice label	Colour based on customer requirements (Please send M-Print PRO file)		
Number of markers per packaging unit	Form of supply	MultiCard	
Size of labelling field	12 x 3.2 mm		
compatible printer	<a href="#">PRINTJET CONNECT</a> , <a href="#">MCP BASIC 2</a> , <a href="#">MCP PLUS 2</a>		
Number of markers per combination	1 MultiCard = Conductor and cable markers		
Operating temperature range	-40...100 °C		

## Conductor and cable markers

Halogen	No	Conductor cross-section, max.	1.5 mm <sup>2</sup>
Conductor cross-section, min.	0.75 mm <sup>2</sup>	Conductor O.D., max.	2.9 mm
Conductor O.D., min.	2.2 mm	Conductor O.D.	2.2 - 2.9 mm
Cross-section for connected wire	0.75 - 1.5 mm <sup>2</sup>		

## Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		