


SFR 2/21 MC SDR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The SlimFix Redesign SFR is a modification of the familiar SlimFix conductor marker which significantly simplifies installation. The marker is simply slid onto the cable and is securely fixed in no time.

General ordering data

Version	SlimFix R, Conductor and cable markers, 2.2 - 2.9 mm, 21 x 5.8 mm, To customer specification
Order No.	1318820000
Type	SFR 2/21 MC SDR
GTIN (EAN)	4050118179576
Qty.	80 items

SFR 2/21 MC SDR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	21 mm	Height (inches)	0.8268 inch
Width	5.8 mm	Width (inches)	0.2283 inch
Net weight	0.25 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.002 kg CO2 eq.	

General data

Number per sheet	80		
Type of printing	To customer specification		
Width	5.8 mm		
UL 94 flammability rating	V-2		
Operating temperature range, max.	100 °C		
Operating temperature range, min.	-40 °C		
Colour	To customer specification		
Halogen	No		
Basic material	Polyamide 66		
Printed characters	Requires M-Print PRO File		
Advice label	Colour based on customer requirements (Please send M-Print PRO file)		
Number of markers per packaging unit	Form of supply	MultiCard	
Size of labelling field	21 x 3.2 mm		
compatible printer	PRINTJET CONNECT , MCP BASIC 2 , MCP PLUS 2		
Number of markers per combination	1 MultiCard = Conductor and cable markers		
Operating temperature range	-40...100 °C		

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	1.5 mm ²
Conductor cross-section, min.	0.75 mm ²	Conductor O.D., max.	2.9 mm
Conductor O.D., min.	2.2 mm	Conductor O.D.	2.2 - 2.9 mm
Cross-section for connected wire	0.75 - 1.5 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		