

**CC-M 30/60 2X3 ST****Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26  
D-32758 Detmold  
Germany[www.weidmueller.com](http://www.weidmueller.com)

MetalliCards are available in aluminium or stainless steel to meet a wide range of labelling requirements. The chrome-coated aluminium tags are the inexpensive alternative for a variety of applications, and in particular, they prove themselves through the deep contrasts of their multi-colour print. In the technologically demanding chemical and process industries, you are on the safe side when using the stainless steel MetalliCard with its outstanding resistance characteristics. Its formats cover the needs of the entire system-identification spectrum. Whether small equipment or type plates, they ensure high-quality marking processes. The MetalliCard also offers optimum installation characteristics. MetalliCards can be used universally thanks to various fixation options: bonding, riveting, with tag holders or rails, or in combination with stainless steel cable ties.

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Version	MetalliCard, Device markers, 30 x 60 mm, silver
Order No.	<a href="#">1327870000</a>
Type	CC-M 30/60 2X3 ST
GTIN (EAN)	4050118132717
Qty.	100 items

## CC-M 30/60 2X3 ST

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

RoHS	Conform
------	---------

## Dimensions and weights

Depth	0.5 mm	Depth (inches)	0.0197 inch
Height	30 mm	Height (inches)	1.1811 inch
Width	60 mm	Width (inches)	2.3622 inch
Net weight	6.7 g		

## Temperatures

Operating temperature range	-55...130 °C
-----------------------------	--------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## General data

Version	pluggable, with 3.5 mm mounting hole
Width	60 mm
Operating temperature range, max.	130 °C
Operating temperature range, min.	-55 °C
Colour	silver
Basic material	Micro-etched stainless steel 1.4301 (ST), Stainless steel 1.4301
Printed characters	without
Number of markers per packaging unit	Form of supply
Size of labelling field	30.2 x 57.2 mm
Recommended industries	Energy, Process
compatible printer	
Number of markers per combination	1 MetalliCard = Device markers
Operating temperature range	-55...130 °C

## Device markers

Drill-hole diameter	3.30 mm
---------------------	---------

## Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

## CC-M 30/60 2X3 ST

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Example of use

