

IE-PS-M12X-P-FH

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems. The IDC is simple and quick to assemble since this technology allows the conductor to be inserted directly into the terminal point, without crimping or having to strip the insulation. It also has excellent functional security.

General ordering data

Version	Plugs prefabricated to customer spec., M12, IDC, Cat.6A / Class EA (ISO/IEC 11801 2010), IP67 plugged
Order No.	1324020000
Type	IE-PS-M12X-P-FH
GTIN (EAN)	4050118127782
Qty.	10 items

IE-PS-M12X-P-FH

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E316369

Dimensions and weights

Diameter	16.8 mm	Net weight	33.95 g
----------	---------	------------	---------

Temperatures

Storage temperature	Operating temperature	-40 °C...85 °C
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

Technical data customisable plug-in connectors

Number of poles	8	Coding	X-coded
Contact surface	Gold-plated	LED	No
Type of connection	Insulation displacement connection	Housing main material	Zinc diecast
Insulation resistance	100 MΩ	Cable diameter, max.	9.7 mm
Cable diameter, min.	5 mm	Category	Cat.6A / Class EA (ISO/IEC 11801 2010)
Contact material	Brass	Conductor cross-section, max.	0.34 mm ²
Conductor cross-section, min.	0.14 mm ²	Nominal voltage	48 V
Nominal current	0.5 A	Protection degree	IP67 plugged
Plugging cycles	≥ 100	Pollution severity	2
Gender of contact	Male	Shield connection	Yes, screwed
Threaded ring material	Zinc diecast, tin plated		

General Info

Number of poles	8	Connection 1	M12
Connection 2	IDC	Wiring	EIA/TIA T568 A, EIA/TIA T568 B
UL 94 flammability rating	V-0	Housing main material	Zinc diecast
Insulation cross-section, max.	1.6 mm	Category	Cat.6A / Class EA (ISO/IEC 11801 2010)
Connection thread	M12	Contact material	Brass
Contact surface	Gold-plated	Wire connection diameter, solid, min.	0.41 mm
Connection diameter, solid	0.41...0.64 mm	Wire connection diameter, solid, max.	0.64 mm
Conductor connection cross-section, solid (AWG)	AWG 26/1...AWG 22/1	Wire cross-section, solid, min. (AWG)	AWG 26/1
Connection diameter, flexible	0.48...0.76 mm	Wire cross-section, solid, max. (AWG)	AWG 22/1
Conductor connection cross-section, flexible (AWG)	AWG 26/7...AWG 22/7	Wire connection diameter, flexible, min.	0.48 mm

Creation date 19.02.2026 02:51:16 MEZ

Catalogue status / Drawings

IE-PS-M12X-P-FH

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Wire connection diameter, flexible, max.	0.76 mm	Wire connection cross section, finely stranded, max.	0.32 mm ²
Wire cross-section, solid, min.	0.34 mm ²	Wire cross-section, solid, max.	0.32 mm ²
Conductor connection cross-section, flexible	...0.32 mm ²	Wire cross-section, finely stranded, min. (AWG)	AWG 26/7
Wire cross-section, finely stranded, max. (AWG)	AWG 22/7	Sheath diameter, min.	5 mm
Sheath diameter, max.	9.7 mm	Contact holder materials	PA
Shielding	360° all-round enclosure	Protection degree	IP67 plugged
Plugging cycles	≥ 100		

Electrical properties

Insulation resistance	100 MΩ	Nominal voltage	48 V
PoE / PoE+	conforming to IEEE 802.3at		

General standards

Connector standard	IEC 61076-2-109	Certificate no. (cULus)	E316369
--------------------	-----------------	-------------------------	---------

Standards


Connector standard	IEC 61076-2-109	Fire safety for railway vehicles	DIN EN 45545-2
--------------------	-----------------	----------------------------------	----------------

Classifications

ETIM 8.0	EC002635	ETIM 9.0	EC002635
ETIM 10.0	EC002635	ECLASS 14.0	27-44-01-16
ECLASS 15.0	27-44-01-16		

Drawings

Dimensioned drawing



Pinning

