

CC-M 27/18 AL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



MetalliCards are available in aluminium or stainless steel to meet a wide range of labelling requirements. The chrome-coated aluminium tags are the inexpensive alternative for a variety of applications, and in particular, they prove themselves through the deep contrasts of their multi-colour print. In the technologically demanding chemical and process industries, you are on the safe side when using the stainless steel MetalliCard with its outstanding resistance characteristics. Its formats cover the needs of the entire system-identification spectrum. Whether small equipment or type plates, they ensure high-quality marking processes. The MetalliCard also offers optimum installation characteristics. MetalliCards can be used universally thanks to various fixation options: bonding, riveting, with tag holders or rails, or in combination with stainless steel cable ties.

For custom printing: Please send us a file of our labelling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	MetalliCard, Device markers, 26.8 x 18 mm, silver
Order No.	1327630000
Type	CC-M 27/18 AL
GTIN (EAN)	4050118132526
Qty.	200 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.5 mm	Depth (inches)	0.0197 inch
Height	26.8 mm	Height (inches)	1.0551 inch
Width	18 mm	Width (inches)	0.7087 inch
Net weight	0.61 g		

Temperatures

Operating temperature range	-55...130 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Size of labelling field	27 x 18 mm		
Version	pluggable		
Width	18 mm		
Operating temperature range, max.	130 °C		
Operating temperature range, min.	-55 °C		
Colour	silver		
Basic material	Anodized aluminium		
Printed characters	without		
Number of markers per packaging unit	Form of supply	MetalliCard	
Size of labelling field	25 x 15 mm		
Recommended industries	Energy, Process		
compatible printer			
Number of markers per combination	1 MetalliCard = Device markers		
Operating temperature range	-55...130 °C		

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

Drawings

Example of use



CC-M 27/18 AL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Accessories

www.weidmueller.com

Complementary products



General ordering data

Type	DKB CC 27/18	Version	
Order No.	1341140000	MetalliCard, Adhesive strip, 27 x 18 mm, Transparent	
GTIN (EAN)	4050118145625		
Qty.	320 ST		
Type	INLAY CC-M 27/18	Version	
Order No.	1341040000		
GTIN (EAN)	4050118145397		
Qty.	1 ST		
Type	INLAY CC-M UNIVERSAL	Version	
Order No.	1341120000		
GTIN (EAN)	4050118145458		
Qty.	1 ST		
Type	PRIMER CC-M	Version	
Order No.	2068020000		
GTIN (EAN)	4050118416534		
Qty.	100 ST		