

PAC-UNIV-HE10-HE10-3M5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

General ordering data

| | |
|------------|----------------------------|
| Version | Pre-assembled cable, PAC |
| Order No. | 1349630035 |
| Type | PAC-UNIV-HE10-HE10-3M5 |
| GTIN (EAN) | 4032248249176 |
| Qty. | 1 items |

PAC-UNIV-HE10-HE10-3M5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | |
|------------|---------|
| Net weight | 129.8 g |
|------------|---------|

Temperatures

| | | | |
|---------------------|-------------|-----------------------|----------|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 |
|---------------------|-------------|-----------------------|----------|

Environmental Product Compliance

| | |
|------------------------|-----------------------|
| RoHS Compliance Status | Compliant |
| REACH SVHC | No SVHC above 0.1 wt% |

General Data

| | | | |
|---------------------|---------------------------------|-----------------------|---------------------------------|
| Cable length | 3.5 m | Suitable for | Digital signals |
| Basic material | PVC | Cable | Cable LiYY |
| Interface connector | FLAT CABLE CONECTOR HE10 10P | Number of poles, min. | 10-pole |
| Outer diameter | 7 ± 1 mm | Connector PLC side | FLAT CABLE CONECTOR HE10 10P |
| Wire cross-section | 0.14 mm ² | | |

Electrical Data

| | | | |
|------------------------|---------------------|---|------------|
| Total current, max. | 3 A | Permissible current strength per path, max. | 1 A |
| Rated voltage | ≤ 60 V DC ≤ 25 V AC | Resistance | ≤ 150 mΩ/m |
| Operating voltage | ≤ 60 V DC ≤ 25 V AC | Capacity wire / wires | 300 pF/m |
| Capacity wire / shield | 300 pF/m | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000237 | ETIM 9.0 | EC000237 |
| ETIM 10.0 | EC000237 | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 | | |