

**PAC-UNIV-HE16-HE16-10M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

**General ordering data**

|            |                            |
|------------|----------------------------|
| Version    | Pre-assembled cable, PAC   |
| Order No.  | <a href="#">1349650100</a> |
| Type       | PAC-UNIV-HE16-HE16-10M     |
| GTIN (EAN) | 4099986579262              |
| Qty.       | 1 items                    |

**PAC-UNIV-HE16-HE16-10M**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Net weight 708 g

**Temperatures**

Storage temperature -10...60 °C Operating temperature -10...50 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant  
 REACH SVHC No SVHC above 0.1 wt%

**General Data**

|                     |                      |                       |                 |
|---------------------|----------------------|-----------------------|-----------------|
| Cable length        | 10 m                 | Suitable for          | Digital signals |
| Basic material      | PVC                  | Cable                 | Cable LiYY      |
| Interface connector | HE10 16P             | Number of poles, min. | 16-pole         |
| Outer diameter      | 8 ± 1 mm             | Connector PLC side    | HE10 16P        |
| Wire cross-section  | 0.14 mm <sup>2</sup> |                       |                 |

**Electrical Data**

|                        |                     |   |            |
|------------------------|---------------------|---|------------|
| Total current, max.    | 3 A                 | Permissible current strength per path, max. | 1 A        |
| Rated voltage          | ≤ 60 V DC ≤ 25 V AC | Resistance                                  | ≤ 150 mΩ/m |
| Operating voltage      | ≤ 60 V DC ≤ 25 V AC | Capacity wire / wires                       | 300 pF/m   |
| Capacity wire / shield | 300 pF/m            |   |            |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000237    | ETIM 9.0    | EC000237    |
| ETIM 10.0   | EC000237    | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 |             |             |