

## PAC-UNIV-HE50-HE50-10M

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

### General ordering data

|            |                            |
|------------|----------------------------|
| Version    | Pre-assembled cable, PAC   |
| Order No.  | <a href="#">1349720100</a> |
| Type       | PAC-UNIV-HE50-HE50-10M     |
| GTIN (EAN) | 4032248347056              |
| Qty.       | 1 items                    |

## PAC-UNIV-HE50-HE50-10M

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |        |
|------------|--------|
| Net weight | 1709 g |
|------------|--------|

### Temperatures

|                     |             |                       |          |
|---------------------|-------------|-----------------------|----------|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 |
|---------------------|-------------|-----------------------|----------|

### Environmental Product Compliance

|                        |                       |
|------------------------|-----------------------|
| RoHS Compliance Status | Compliant             |
| REACH SVHC             | No SVHC above 0.1 wt% |

### General Data

|                     |                      |                       |                 |
|---------------------|----------------------|-----------------------|-----------------|
| Cable length        | 10 m                 | Suitable for          | Digital signals |
| Basic material      | PVC                  | Cable                 | Cable LiYY      |
| Interface connector | HE10 50 P            | Number of poles, min. | 50-pole         |
| Outer diameter      | 13.4 ± 1 mm          | Connector PLC side    | HE10 50 P       |
| Wire cross-section  | 0.14 mm <sup>2</sup> |                       |                 |

### Electrical Data

|                        |                     |   |            |
|------------------------|---------------------|---|------------|
| Total current, max.    | 3 A                 | Permissible current strength per path, max. | 1 A        |
| Rated voltage          | ≤ 60 V DC ≤ 25 V AC | Resistance                                  | ≤ 150 mΩ/m |
| Operating voltage      | ≤ 60 V DC ≤ 25 V AC | Capacity wire / wires                       | 300 pF/m   |
| Capacity wire / shield | 300 pF/m            |   |            |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000237    | ETIM 9.0    | EC000237    |
| ETIM 10.0   | EC000237    | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 |             |             |