
Data sheet

# PAC-UNIV-HE14-F-2M5

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

## General ordering data

| | |
|---|---|
| Version | Pre-assembled cable, PAC |
| Order No. | 1349740025 |
| Type | PAC-UNIV-HE14-F-2M5 |
| GTIN (EAN) | 4099986579460 |
| Qty. | 1 items |

# Data sheet

## PAC-UNIV-HE14-F-2M5

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Technical data

### Approvals

| | |
|---|---|
| ROHS | Conform |

### Dimensions and weights

| | |
|---|---|
| Net weight | 177 g |

### Temperatures

| | | | |
|---|---|---|---|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 °C |

### Environmental Product Compliance

| | |
|---|---|
| RoHS Compliance Status | Compliant |
| REACH SVHC | No SVHC above 0.1 wt% |

### General Data

| | | | |
|---|---|---|---|
| Cable length | 2.5 m | Suitable for | Digital signals |
| Basic material | PVC | Cable | Cable LiYY |
| Interface connector | FLAT CABLE CONECTOR HE10 14P | Number of poles, min. | 14-pole |
| Outer diameter | 7,6 ± 1 mm | Connector PLC side | H0.14/10 (FERRULES 0.14mm²) |
| Wire cross-section | 0.14 mm² | | |

### Electrical Data

| | | | |
|---|---|---|---|
| Total current, max. | 3 A | Permissible current strength per path, max. | 1 A |
| Rated voltage | ≤ 60 V DC ≤ 25 V AC | Resistance | ≤ 150 mΩ/m |
| Operating voltage | ≤ 60 V DC ≤ 25 V AC | Capacity (wire / wires) | 300 pF/m |
| Capacity (wire / shield) | 300 pF/m | | |

### Rated data UL

| | |
|---|---|
| Total current, max. | 3 A |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC000237 | ETIM 9.0 | EC000237 |
| ETIM 10.0 | EC000237 | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 | | |