

**PAC-UNIV-D25M-D25F-4M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Similar to illustration

**General ordering data**

|            |   |
|------------|---|
| Version    | Pre-assembled cable, PAC, Cable LiYCY, 10.15 ± 1 mm |
| Order No.  | <a href="#">1349980040</a>                          |
| Type       | PAC-UNIV-D25M-D25F-4M                               |
| GTIN (EAN) | 4032248207442                                       |
| Qty.       | 1 items   |

**PAC-UNIV-D25M-D25F-4M**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Net weight 742 g

**Temperatures**

Storage temperature -10...60 °C      Operating temperature -10...50

**Environmental Product Compliance**

RoHS Compliance Status Compliant  
 REACH SVHC Lead 7439-92-1  
 SCIP 4bbf2c0d-0764-4fc8-bb24-9351c28c190d

**General Data**

|                     |                      |                       |                  |
|---------------------|----------------------|-----------------------|------------------|
| Cable length        | 4 m                  | Suitable for          | Analogue signals |
| Basic material      | PVC                  | Cable                 | Cable LiYCY      |
| Interface connector | SUB-D MALE 25P       | Number of poles, min. | 25-pole          |
| Outer diameter      | 10.15 ± 1 mm         | Connector PLC side    | SUB-D FEMALE 25P |
| Wire cross-section  | 0.25 mm <sup>2</sup> |                       |                  |

**Electrical Data**

|                        |                     |   |           |
|------------------------|---------------------|---|-----------|
| Total current, max.    | 3 A                 | Permissible current strength per path, max. | 1 A       |
| Rated voltage          | ≤ 60 Vdc ≤ 25 Vac   | Resistance                                  | ≤ 80 mΩ/m |
| Operating voltage      | ≤ 60 V DC ≤ 25 V AC | Capacity wire / wires                       | 300 pF/m  |
| Capacity wire / shield | 300 pF/m            |   |           |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000237    | ETIM 9.0    | EC000237    |
| ETIM 10.0   | EC000237    | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 |             |             |