

## PAC-UNIV-D37F-F-0M5

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

### General ordering data

|            |                                                    |
|------------|----------------------------------------------------|
| Version    | Pre-assembled cable, PAC, Cable LiYCY, 12.2 ± 1 mm |
| Order No.  | <a href="#">1350500005</a>                         |
| Type       | PAC-UNIV-D37F-F-0M5                                |
| GTIN (EAN) | 4099986580992                                      |
| Qty.       | 1 items                                            |

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Net weight 361.82 g

**Temperatures**

Storage temperature -10...60 °C      Operating temperature -10...50 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant  
 REACH SVHC No SVHC above 0.1 wt%

**General Data**

|                     |                      |                       |                                          |
|---------------------|----------------------|-----------------------|------------------------------------------|
| Cable length        | 0.5 m                | Suitable for          | Analogue signals                         |
| Basic material      | PVC                  | Cable                 | Cable LiYCY                              |
| Interface connector | SUB-D FEMALE 37P     | Number of poles, min. | 37-pole                                  |
| Outer diameter      | 12.2 ± 1 mm          | Connector PLC side    | H0.25/10 (FERRULES 0.25mm <sup>2</sup> ) |
| Wire cross-section  | 0.25 mm <sup>2</sup> |                       |                                          |

**Electrical Data**

|                        |                     |                                             |           |
|------------------------|---------------------|---------------------------------------------|-----------|
| Total current, max.    | 3 A                 | Permissible current strength per path, max. | 1 A       |
| Rated voltage          | ≤ 60 Vdc ≤ 25 Vac   | Resistance                                  | ≤ 80 mΩ/m |
| Operating voltage      | ≤ 60 V DC ≤ 25 V AC | Capacity wire / wires                       | 300 pF/m  |
| Capacity wire / shield | 300 pF/m            |                                             |           |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000237    | ETIM 9.0    | EC000237    |
| ETIM 10.0   | EC000237    | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 |             |             |