

PAC-UNIV-D50F-F-10M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

General ordering data

| | |
|------------|--|
| Version | Pre-assembled cable, PAC, Cable LiYCY, 14,2 ± 1 mm |
| Order No. | 1350520100 |
| Type | PAC-UNIV-D50F-F-10M |
| GTIN (EAN) | 403224839255 1 |
| Qty. | 1 items |

PAC-UNIV-D50F-F-10M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Net weight 3849.1 g

Temperatures

Storage temperature -10...60 °C Operating temperature -10...50

Environmental Product Compliance

RoHS Compliance Status Compliant
 REACH SVHC No SVHC above 0.1 wt%

General Data

| | | | |
|---------------------|----------------------|-----------------------|--|
| Cable length | 10 m | Suitable for | Analogue signals |
| Basic material | PVC | Cable | Cable LiYCY |
| Interface connector | SUB-D FEMALE 50P | Number of poles, min. | 50-pole |
| Outer diameter | 14,2 ± 1 mm | Connector PLC side | H0.25/10 (FERRULES 0.25mm ²) |
| Wire cross-section | 0.25 mm ² | | |

Electrical Data

| | | | |
|------------------------|---------------------|---|-----------|
| Total current, max. | 3 A | Permissible current strength per path, max. | 1 A |
| Rated voltage | ≤ 60 Vdc ≤ 25 Vac | Resistance | ≤ 80 mΩ/m |
| Operating voltage | ≤ 60 V DC ≤ 25 V AC | Capacity wire / wires | 300 pF/m |
| Capacity wire / shield | 300 pF/m | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000237 | ETIM 9.0 | EC000237 |
| ETIM 10.0 | EC000237 | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 | | |