

VPU III R 24V/4KV AC/DC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Type III surge protection

- Compact Type III arrester for AC/DC protection acc. to IEC 61643-11:2012
- Suitable for protecting terminals
- Installed in the vicinity of the equipment to be protected
- Can be used as single-port arrester when nominal current is greater than 16 A

General ordering data

Version	Surge voltage arrester, Low voltage, with remote contact, Single-phase
Order No.	1351580000
Type	VPU III R 24V/4KV AC/DC
GTIN (EAN)	4050118158557
Qty.	1 items

VPU III R 24V/4KV AC/DC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	71.5 mm	Depth (inches)	2.815 inch
Height	102 mm	Height (inches)	4.0157 inch
Width	18 mm	Width (inches)	0.7087 inch
Net weight	84 g		

Temperatures

Storage temperature	-40 °C...70 °C	Operating temperature	-40 °C...70 °C
Humidity	5 - 95% rel. humidity		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Connection data, remote alert

Cross-section for connected wire, solid core, min.	0.2 mm ²	Stripping length	5 mm
Connection type	Screw connection	Cross-section for connected wire, solid core, max.	1.5 mm ²
Max. torque	0.5 Nm		

General data

Optical function display	Green LED = OK, Red LED = arrester is defective, replace	Segment	Power distribution
Version	with remote contact	Design	Installation housing; 1TE, Insta IP 20
UL 94 flammability rating	V-0	Colour	orange
Protection degree	IP20	Mounting rail	TS 35
Operating altitude	≤ 3000 m		

Insulation coordination acc. to EN 50178

Surge voltage category	II	Pollution severity	2
------------------------	----	--------------------	---

Rated data IEC / EN

Number of poles	2	Combined pulse UOC	4 kV
Leakage current at Un	30 µA	Signalling contact	250 V 10 A 1 NC
Rated voltage (AC)	24 V	Rated voltage (DC)	32 V
Rated current I _N	16 A	Low voltage network	Single-phase
Mains frequency at 250 V _{max}	50...60Hz	Voltage type	AC/DC
Temporary surge voltage (over-voltage) - TOV	46 V	Fuse protection	16 A

VPU III R 24V/4KV AC/DC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Response time / fallback time	≤ 100 ns	Standards	IEC 61643-11, EN 61643-11
Requirements class, acc. to EN 61643-11	T3	Requirements category acc. to IEC 61643-11	Type III
Max. continuous voltage, U _c (AC)	32 V	Energy coordination (≤10 m)	Type II, Type III
Protection level U _p at IN (L/N-PE)	≤ 0.9 kV	Short-circuit current rating ISCCR	1.5 kA
Discharge current (type III)	4 kA	Integrated back-up fuse	No
PE conductor current IPE	30 µA		

Connection data

Stripping length	7 mm	Type of connection	Screw connection
Stripping length, rated connection	7 mm	Tightening torque, min.	0.4 Nm
Tightening torque, max.	0.5 Nm	Clamping range, rated connection	2.5 mm ²
Clamping range, min.	0.5 mm ²	Clamping range, max.	2.5 mm ²
Wire cross-section, solid, min.	0.13 mm ²	Wire cross-section, solid, max.	2.5 mm ²
Wire connection cross section, finely stranded, min.	0.5 mm ²	Wire connection cross section, finely stranded, max.	2.5 mm ²
Conductor cross-section, flexible, AEH (DIN 46228-1), min.	0.5 mm ²	Conductor cross-section, flexible, AEH (DIN 46228-1), max.	2.5 mm ²
Connection cross-section, stranded, min. 0.5 mm ²		Connection cross-section, stranded, max.	2.5 mm ²

Electrical data

Voltage type	AC/DC
--------------	-------

General data

Number of poles	2	Protection degree	IP20
Colour	orange		


Guarantee

Time interval	5 years
---------------	---------

Classifications

ETIM 8.0	EC000942	ETIM 9.0	EC000942
ETIM 10.0	EC000942	ECLASS 14.0	27-17-12-03
ECLASS 15.0	27-17-12-03		

Electric symbol



Schematic circuit diagram