

**PAC-UNIV-HE34-F-6M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Similar to illustration

**General ordering data**

|            |                            |
|------------|----------------------------|
| Version    | Pre-assembled cable, PAC   |
| Order No.  | <a href="#">1349840060</a> |
| Type       | PAC-UNIV-HE34-F-6M         |
| GTIN (EAN) | 4032248209002              |
| Qty.       | 1 items                    |

**PAC-UNIV-HE34-F-6M**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Net weight 725 g

**Temperatures**

Storage temperature -10...60 °C      Operating temperature -10...50

**Environmental Product Compliance**

RoHS Compliance Status Compliant  
 REACH SVHC No SVHC above 0.1 wt%

**General Data**

|                     |                                 |                       |   |
|---------------------|---------------------------------|-----------------------|---|
| Cable length        | 6 m                             | Suitable for          | Digital signals                             |
| Basic material      | PVC                             | Cable                 | Cable LiYY                                  |
| Interface connector | FLAT CABLE CONECTOR<br>HE10 34P | Number of poles, min. | 34-pole                                     |
| Outer diameter      | 11 ± 1 mm                       | Connector PLC side    | H0.14/10 (FERRULES<br>0.14mm <sup>2</sup> ) |
| Wire cross-section  | 0.14 mm <sup>2</sup>            |                       |   |

**Electrical Data**

|                        |                     |   |            |
|------------------------|---------------------|---|------------|
| Total current, max.    | 3 A                 | Permissible current strength per path, max. | 1 A        |
| Rated voltage          | ≤ 60 V DC ≤ 25 V AC | Resistance                                  | ≤ 150 mΩ/m |
| Operating voltage      | ≤ 60 V DC ≤ 25 V AC | Capacity wire / wires                       | 300 pF/m   |
| Capacity wire / shield | 300 pF/m            |   |            |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000237    | ETIM 9.0    | EC000237    |
| ETIM 10.0   | EC000237    | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 |             |             |