Data sheet

SAIE-M12S-4-0.2U P9 .75

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact A-, K-, L-, S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

General ordering data

Version	Built-in plugs, M12, pin, straight, Mounting thread: PG 9, Number of poles: 4, Strand / cable length: 0.2 m, Front mounting
Order No.	1353770000
Type	SAIE-M12S-4-0.2U P9 .75
GTIN (EAN)	4050118156195
Qty.	1 items

SAIE-M12S-4-0.2U P9 .75

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals	
ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E307231

Dimensions and weights

Net weight	18.3 g

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1, Terphenyl, hydrogenated 61788-32-7, 4,4'-isopropylidenediphenol 80-05-7
SCIP	1852c6ab-96c4-45bf-9300-a5a27aab9a83

Technical specifications for cable

PE function	No	Wire cross section (Print/Online)	AWG 18
Strand / cable length	0.2 m	Core cross-section AWG	AWG 18
Colour coding	brown, white, blue, black	Number of poles	4

Technical data customisable plug-in connectors

Number of poles	4	Coding	A-coded
Contact surface	Gold-plated	Housing main material	Brass, nickel-plated
Nominal voltage	250 V	Nominal current	8 A
Protection degree	IP67, when screwed in	Plugging cycles	≥ 100
Cable gland	PG 9	Rated current	Contacts 1-4 8A, contact 5 2A
Temperature range of housing	-40 … +85 ° C		

Standards

Connector standard	IEC 61076-2-101

General data

Number of poles	4	Coding	A-coded
Connection thread	M12	Contact surface	Gold-plated
Housing main material	Brass, nickel-plated	Type of mounting	Front mounting
Nominal voltage	250 V	Nominal current	8 A
Protection degree	IP67, when screwed in	Plugging cycles	≥ 100
Cable gland	PG 9	Rated voltage	250 V (4-pole) / 60 V (5-pole)
Rated current	Contacts 1-4 8A, contact 5 2A	Wire cross section (Print/Online)	AWG 18
Connection 1	M12	Connection 2	Flying wires
Strand / cable length	0.2 m	Mounting thread	PG 9
Temperature range of housing	-40 … +85 ° C	Conductor O.D.	-

SAIE-M12S-4-0.2U P9 .75

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Classifications

ETIM 8.0	EC003570	ETIM 9.0	EC003570
ETIM 10.0	EC003570	ECLASS 14.0	27-44-01-03
ECLASS 15.0	27-44-01-03		

SAIE-M12S-4-0.2U P9 .75

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Pole scheme

