

SAIE-M12S-4-0.2U P9 .75**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact A-, K-, L-, S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

General ordering data

Version	Built-in plugs, M12, pin, straight, Mounting thread: PG 9, Number of poles: 4, Strand / cable length: 0.2 m, Front mounting
Order No.	1353770000
Type	SAIE-M12S-4-0.2U P9 .75
GTIN (EAN)	4050118156195
Qty.	1 items

SAIE-M12S-4-0.2U P9 .75

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals	CURUS
ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E307231

Dimensions and weights

Net weight	18.3 g
------------	--------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1, Terphenyl, hydrogenated 61788-32-7, 4,4'-isopropylidenediphenol 80-05-7
SCIP	1852c6ab-96c4-45bf-9300-a5a27aab9a83

Technical specifications for cable

PE function	No	Wire cross section (Print/Online)	AWG 18
Strand / cable length	0.2 m	Core cross-section AWG	AWG 18
Colour coding	brown, white, blue, black	Number of poles	4

Technical data customisable plug-in connectors

Number of poles	4	Coding	A-coded
Contact surface	Gold-plated	Housing main material	Brass, nickel-plated
Nominal voltage	250 V	Nominal current	8 A
Protection degree	IP67, when screwed in	Plugging cycles	≥ 100
Cable gland	PG 9	Rated current	Contacts 1-4 8A, contact 5 2A
Temperature range of housing	-40 ... +85 °C		

Standards

Connector standard	IEC 61076-2-101
--------------------	-----------------

General data

Number of poles	4	Coding	A-coded
Connection thread	M12	Contact surface	Gold-plated
Housing main material	Brass, nickel-plated	Type of mounting	Front mounting
Nominal voltage	250 V	Nominal current	8 A
Protection degree	IP67, when screwed in	Plugging cycles	≥ 100
Cable gland	PG 9	Rated voltage	250 V (4-pole) / 60 V (5-pole)
Rated current	Contacts 1-4 8A, contact 5 2A	Wire cross section (Print/Online)	AWG 18
Connection 1	M12	Connection 2	Flying wires
Strand / cable length	0.2 m	Mounting thread	PG 9
Temperature range of housing	-40 ... +85 °C	Conductor O.D.	-

Classifications

ETIM 8.0	EC003570	ETIM 9.0	EC003570
ETIM 10.0	EC003570	ECLASS 14.0	27-44-01-03

SAIE-M12S-4-0.2U P9 .75

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Technical data

ECLASS 15.0

27-44-01-03

Pole scheme



SAIE-M12S-4-0.2U P9 .75

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Brass lock nuts, nickel-plated



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU PG9-MS	Version	
Order No.	1694080000	SKMU MS (brass locknut), Locknut, PG 9, 2.8 mm, Brass, nickel-plated	
GTIN (EAN)	4008190872243		
Qty.	100 ST		