

PAC-M340-UNIU-V0-1M5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

With help of this cabling system for the key Siemens S7-300 and S7-400 input/output cards, users can design a byte-connection system for both digital inputs and outputs. This system consists of:

- Cable with front adapter for the PLC and standard flat cable connectors for the interface.
- Passive interface or per-relay in byte mode (shared supply in groups of eight signals).
- The main advantages of this system:
 - Quicker project planning and initial commissioning.
 - Saves time during the installation.
 - Space-saving.
 - Elimination of wiring mistakes.

General ordering data

Version	Cable LiYY, 0.25 mm ²
Order No.	1355950015
Type	PAC-M340-UNIU-V0-1M5
GTIN (EAN)	4099986581081
Qty.	1 items

PAC-M340-UNI-U-V0-1M5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Net weight	249 g
------------	-------

Temperatures

Storage temperature	-10...60 °C	Operating temperature	-10...50 °C
---------------------	-------------	-----------------------	-------------

General Data

Cable length	1.5 m	Suitable for	Digital signals
Basic material	PVC	Cable	Cable LiYY
Interface connector	H0.25 (FERRULES 0.25mm ²)	Number of poles, min.	20-pole
Outer diameter	8.6 ± 1 mm	Connector PLC side	SCHNEIDER BMX FTB 2000 20P
Wire cross-section	0.25 mm ²		

Electrical Data

Total current, max.	3 A	High voltage test	1 KV/1s
Permissible current strength per path, max.	1 A	Rated voltage	≤ 250 V DC ≤ 250 V AC
Resistance	≤ 80 mΩ/m	Operating voltage	≤ 60 V DC ≤ 25 V AC
Capacity (wire / wires)	300 pF/m		

Rated data UL

Total current, max.	3 A
---------------------	-----

Classifications

ETIM 8.0	EC000237	ETIM 9.0	EC000237
ETIM 10.0	EC000237	ECLASS 14.0	27-24-22-20
ECLASS 15.0	27-24-22-20		