

## PAC-UNIV-D9F-F-5M

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

### General ordering data

|            |   |
|------------|---|
| Version    | Pre-assembled cable, PAC, Cable LiYCY, 7,8 ± 1 mm |
| Order No.  | <a href="#">1350470050</a>                        |
| Type       | PAC-UNIV-D9F-F-5M                                 |
| GTIN (EAN) | 4032248271047                                     |
| Qty.       | 1 items   |

**PAC-UNIV-D9F-F-5M**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Net weight 782.3 g

**Temperatures**

Storage temperature -10...60 °C      Operating temperature -10...50

**Environmental Product Compliance**

RoHS Compliance Status Compliant  
 REACH SVHC No SVHC above 0.1 wt%

**General Data**

|                     |                      |                       |  |
|---------------------|----------------------|-----------------------|--|
| Cable length        | 5 m                  | Suitable for          | Analogue signals                         |
| Basic material      | PVC                  | Cable                 | Cable LiYCY                              |
| Interface connector | SUB-D FEMALE 9P      | Number of poles, min. | 9-pole                                   |
| Outer diameter      | 7,8 ± 1 mm           | Connector PLC side    | H0.25/10 (FERRULES 0.25mm <sup>2</sup> ) |
| Wire cross-section  | 0.25 mm <sup>2</sup> |                       |  |

**Electrical Data**

|                        |                     |   |           |
|------------------------|---------------------|---|-----------|
| Total current, max.    | 3 A                 | Permissible current strength per path, max. | 1 A       |
| Rated voltage          | ≤ 60 Vdc ≤ 25 Vac   | Resistance                                  | ≤ 80 mΩ/m |
| Operating voltage      | ≤ 60 V DC ≤ 25 V AC | Capacity wire / wires                       | 300 pF/m  |
| Capacity wire / shield | 300 pF/m            |   |           |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000237    | ETIM 9.0    | EC000237    |
| ETIM 10.0   | EC000237    | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 |             |             |