

**VPU II 0 PV 1000V DC**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



**General ordering data**

Version	Surge voltage arrester, Low voltage, Accessories, Surge protection II
Order No.	<a href="#">1351190000</a>
Type	VPU II 0 PV 1000V DC
GTIN (EAN)	4050118158847
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2026-06-01T00:00:00+02:00
Alternative product	<a href="#">VPU PV II 0 1000</a>

## VPU II 0 PV 1000V DC

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

Depth	64 mm	Depth (inches)	2.5197 inch
Height	52 mm	Height (inches)	2.0472 inch
Width	17.8 mm	Width (inches)	0.7008 inch
Net weight	90.64 g		

### Temperatures

Storage temperature -40 °C...80 °C      Operating temperature -40 °C...

### Environmental Product Compliance

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

### General data

Optical function display	green = OK; red = arrester is defective - replace	Version	Surge protection II
Design	Installation housing; 1TE, Insta IP 20	UL 94 flammability rating	V-0
Colour	orange	Protection degree	IP20
Mounting rail	TS 35		

### Insulation coordination acc. to EN 50178

Surge voltage category III      Pollution severity 2

### Photovoltaic technical data

Standards	EN 50539-11	Protection level Up (+/-, -/PE, +/-PE)	≤ 2.6 kV
Short-circuit current ISCP	200 A	Requirements class	Type II
Protection level Up at IN (per module)	≤ 2.8 kV	PV system voltage, max. Ucpv	1000 V
Maximum continuous operating voltage DC UCPV mode +/-, -/PE, +/-PE	1000 V		

### Rated data IEC / EN

Number of poles	1	Leakage current at Un	30 µA
Rated voltage (DC)	1000 V	PV voltage, acc. to IEC 60364-7-712	≤ 1000 V
Voltage type	DC	Response time / fallback time	≤ 25 ns
Standards	EN 50539-11	Max. continuous voltage, Uc (DC)	1000 V
Discharge current In (8/20µs) wire-PE	12.5 kA	Discharge current I <sub>max</sub> (8/20µs) wire-PE	25 kA
Protection level Up at IN (L/N-PE)	≤ 2.8 kV	Integrated back-up fuse	No

## VPU II 0 PV 1000V DC

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Connection data

Type of connection	pluggable	Wire connection cross section, finely stranded, min.	1.5 mm <sup>2</sup>
Wire connection cross section, finely stranded, max.	25 mm <sup>2</sup>	Connection cross-section, stranded, min.	1.5 mm <sup>2</sup>
Connection cross-section, stranded, max.	35 mm <sup>2</sup>		

### Electrical data


Voltage type	DC		
--------------	----	--	--

### General data


Number of poles	1	Protection degree	IP20
Colour	orange		

### Classifications

ETIM 8.0	EC000941	ETIM 9.0	EC000941
ETIM 10.0	EC000941	ECLASS 14.0	27-17-90-90
ECLASS 15.0	27-17-90-90		



Circuit diagram

**Accessories****Crosshead screwdriver Phillips**

VDE insulated crosshead screwdriver, for Phillips screws, SDIK PH DIN 7438, ISO 8764/2-PH, output to ISO 8764-PH, SoftFinish grip

**General ordering data**

Type	SDIK PH1 X 80	Version	
Order No.	<a href="#">2749890000</a>	Screwdriver, Blade width (B): 1 mm, 80 mm, Blade thickness (A): 1	
GTIN (EAN)	4050118897098		
Qty.	1 ST		

**Slotted screwdriver**

VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

**General ordering data**

Type	SDIS 1.0X5.5X125	Version	
Order No.	<a href="#">2749850000</a>	Screwdriver, Blade width (B): 5.5 mm, Blade length: 125 mm, Blade thickness (A): 1 mm	
GTIN (EAN)	4050118897050		
Qty.	1 ST		