

## VPU III R 230V/6KV AC

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



### Type III surge protection

- Compact Type III arrester for AC/DC protection acc. to IEC 61643-11:2012
- Suitable for protecting terminals
- Installed in the vicinity of the equipment to be protected
- Can be used as single-port arrester when nominal current is greater than 16 A

### General ordering data

Version	Surge voltage arrester, Low voltage, with remote contact, Single-phase
Order No.	<a href="#">1351650000</a>
Type	VPU III R 230V/6KV AC
GTIN (EAN)	4050118158496
Qty.	1 items

**VPU III R 230V/6KV AC**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Depth	71.5 mm	Depth (inches)	2.815 inch
Height	102 mm	Height (inches)	4.0157 inch
Width	18 mm	Width (inches)	0.7087 inch
Net weight	77 g		

**Temperatures**

Storage temperature	-40 °C...70 °C	Operating temperature	-40 °C...70 °C
Humidity	5 - 95% rel. humidity		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Connection data, remote alert**

Cross-section for connected wire, solid core, min.	0.2 mm <sup>2</sup>	Stripping length	5 mm
Connection type	Screw connection	Cross-section for connected wire, solid core, max.	1.5 mm <sup>2</sup>
Max. torque	0.5 Nm		

**General data**

Optical function display	Green LED = OK, Red LED = arrester is defective, replace	Segment	Power distribution
Version	with remote contact	Design	Installation housing; 1TE, Insta IP 20
UL 94 flammability rating	V-0	Colour	orange
Protection degree	IP20	Mounting rail	TS 35

**Insulation coordination acc. to EN 50178**

Surge voltage category	II	Pollution severity	2
------------------------	----	--------------------	---

**Rated data IEC / EN**

Number of poles	2	Combined pulse UOC	6 kV
Leakage current at Un	30 µA	Signalling contact	250 V 10 A 1 NC
Rated voltage (AC)	230 V	Rated current I <sub>N</sub>	16 A
Low voltage network	Single-phase	Mains frequency at 250 V <sub>max</sub>	50...60Hz
Voltage type	AC	Temporary surge voltage (over-voltage) - TOV	438 V
Fuse protection	16 A	Response time / fallback time	≤ 100 ns

## VPU III R 230V/6KV AC

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

### Technical data

Frequency range, max.	60 Hz	Frequency range, min.	50 Hz
Standards	IEC 61643-11, EN 61643-11	Requirements class, acc. to EN 61643-11	T3
Requirements category acc. to IEC 61643-11	Type III	Max. continuous voltage, U <sub>c</sub> (AC)	300 V
Energy coordination (≤10 m)	Type II, Type III	Protection level U <sub>p</sub> at IN (L/N-PE)	≤ 1.8 kV
Short-circuit current rating ISCCR	1.5 kA	Discharge current (type III)	3 kA
Integrated back-up fuse	No	PE conductor current IPE	30 μA

### Connection data

Stripping length	7 mm	Type of connection	Screw connection
Stripping length, rated connection	7 mm	Tightening torque, min.	0.4 Nm
Tightening torque, max.	0.5 Nm	Clamping range, rated connection	2.5 mm <sup>2</sup>
Clamping range, min.	0.5 mm <sup>2</sup>	Clamping range, max.	2.5 mm <sup>2</sup>
Wire cross-section, solid, min.	0.13 mm <sup>2</sup>	Wire cross-section, solid, max.	2.5 mm <sup>2</sup>
Wire connection cross section, finely stranded, min.	0.5 mm <sup>2</sup>	Wire connection cross section, finely stranded, max.	2.5 mm <sup>2</sup>
Conductor cross-section, flexible, AEH (DIN 46228-1), min.	0.5 mm <sup>2</sup>	Conductor cross-section, flexible, AEH (DIN 46228-1), max.	2.5 mm <sup>2</sup>
Connection cross-section, stranded, min.	0.5 mm <sup>2</sup>	Connection cross-section, stranded, max.	2.5 mm <sup>2</sup>

### Electrical data

Voltage type	AC
--------------	----

### General data

Number of poles	2	Protection degree	IP20
Colour	orange		


### Guarantee

Time interval	5 years
---------------	---------

### Classifications

ETIM 8.0	EC000942	ETIM 9.0	EC000942
ETIM 10.0	EC000942	ECLASS 14.0	27-17-12-03
ECLASS 15.0	27-17-12-03		

Electric symbol



Schematic circuit diagram

## VPU III R 230V/6KV AC

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Crosshead screwdriver Phillips



VDE insulated crosshead screwdriver, for Phillips screws, SDIK PH DIN 7438, ISO 8764/2-PH, output to ISO 8764-PH, SoftFinish grip

### General ordering data

Type	SDIK PH0 X 60	Version	
Order No.	<a href="#">2749880000</a>	Screwdriver, Blade width (B): 0 mm, 60 mm, Blade thickness (A): 0	
GTIN (EAN)	4050118897081		
Qty.	1 ST		