



## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

Depth	25 mm	Depth (inches)	0.9842 inch
Height	35 mm	Height (inches)	1.378 inch
Width	12 mm	Width (inches)	0.4724 inch
Net weight	18 g		

### Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-25 °C...55 °C
Humidity	5 - 95% rel. humidity		

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Connection data, remote alert

Cross-section for connected wire, solid core, min.	0.25 mm <sup>2</sup>	Connection type	Miscellaneous
Cross-section for connected wire, solid core, max.	1.5 mm <sup>2</sup>		

### General data

Optical function display	Green LED = OK, Red LED = arrester is defective, replace	Segment	Power distribution
Version	without telecomm. contact	Design	Flush mounting
UL 94 flammability rating	V-0	Colour	black
Protection degree	IP20		

### Insulation coordination acc. to EN 50178

Surge voltage category	II	Pollution severity	2
------------------------	----	--------------------	---

### Rated data IEC / EN

Number of poles	2	Combined pulse UOC	3 kV
Leakage current at Un	30 µA	Signalling contact	No
Rated voltage (AC)	230 V	Low voltage network	Single-phase
Mains frequency at 250 Vmax	50...60Hz	Voltage type	AC
Temporary surge voltage (over-voltage) - TOV	440 V	Fuse protection	16 A
Response time / fallback time	<100µs	Frequency range, max.	60 Hz
Frequency range, min.	50 Hz	Standards	IEC 61643-11, EN 61643-11
Requirements class, acc. to EN 61643-11	T3	Requirements category acc. to IEC 61643-11	Type III

## VPU III SO LD

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

Max. continuous voltage, U <sub>c</sub> (AC)	275 V	Energy coordination (≤10 m)	Type II, Type III
Protection level Up at IN (L/N-PE)	≤ 1.5 kV	Short-circuit current rating ISCCR	1.5 kA
Discharge current (type III)	3 kA	Integrated back-up fuse	No
PE conductor current IPE	10 μA		

### Electrical data

Voltage type AC

### General data

Number of poles	2	Protection degree	IP20
Colour	black		

### Guarantee


Time interval 5 years

### Classifications

ETIM 8.0	EC000942	ETIM 9.0	EC000942
ETIM 10.0	EC000942	ECLASS 14.0	27-17-12-03
ECLASS 15.0	27-17-12-03		

Drawings

Electric symbol



Schematic circuit diagram