


DEK 5/3.5 MC NE GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	Dekafix, Terminal marker, 5 x 3.5 mm, Pitch in mm (P): 3.50 Weidmueller, yellow
Order No.	1369480000
Type	DEK 5/3.5 MC NE GE
GTIN (EAN)	4050118171860
Qty.	500 items

DEK 5/3.5 MC NE GE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	5 mm	Height (inches)	0.1968 inch
Width	3.5 mm	Width (inches)	0.1378 inch
Net weight	0.15 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.001 kg CO2 eq.	

General data

Orientation of print	horizontal and vertical			
Width	3.5 mm			
UL 94 flammability rating	V-2			
Operating temperature range, max.	100 °C			
Operating temperature range, min.	-40 °C			
Colour	yellow			
Halogen	No			
Basic material	Polyamide 66			
Printed characters	neutral			
Number of markers per packaging unit	Form of supply	MultiCard		
compatible printer	PRINTJET CONNECT , MCP BASIC 2 , MCP PLUS 2			
Number of markers per combination	1 MultiCard = Terminal marker			
Operating temperature range	-40...100 °C			
Application/manufacturer	Weidmueller			

Connector markers

Pitch in mm (P)	3.50 mm
-----------------	---------

Classifications

ETIM 8.0	EC000761	ETIM 9.0	EC000761
ETIM 10.0	EC000761	ECLASS 14.0	27-28-11-01
ECLASS 15.0	27-28-11-01		

Drawings



Drawing

