

TBY-C3-UNIV-SP-2KS-S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

Analogue interfaces are equipped with 40-pole connectors (KS). Versions are available with disconnecting plugs and test points which are extremely useful for voltage and current measurements. There are also versions with useful additional pins for customers who wish to incorporate other elements (resistor ...) for converting voltage/current or monitoring the current loop.

General ordering data

| | |
|-----------------|---|
| Version | Interface, RS, 2 x KS (40P), LL2N 5.08 mm |
| Order No. | 1371640000 |
| Type | TBY-C3-UNIV-SP-2KS-S |
| GTIN (EAN) | 4050118206791 |
| Qty. | 1 items |
| Delivery status | This article will no longer be available in the future. |
| Available until | 2026-02-10T00:00:00+01:00 |

TBY-C3-UNIV-SP-2KS-S

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data
Approvals

Approvals



ROHS Conform

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 70 mm | Depth (inches) | 2.7559 inch |
| Height | 109 mm | Height (inches) | 4.2913 inch |
| Width | 112 mm | Width (inches) | 4.4094 inch |
| Net weight | 220.6 g | | |

Temperatures

| | | | |
|---------------------|-------------|-----------------------|-------------|
| Storage temperature | -40...85 °C | Operating temperature | -25...70 °C |
|---------------------|-------------|-----------------------|-------------|

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | f9d70a48-3ece-4d71-ba78-a0d617266ffc |

General data

| | | | |
|--------------------------------|----------------|----------------------------------|----|
| LED status display per channel | No | Disconnection per channel | No |
| Type of test point | Soldering tags | Contactor | No |
| Fuse per channel | No | LED status of the supply voltage | No |
| Power supply fuse | No | | |

Connection data

| | | | |
|--------------------------------|--------------|-------------------------|--------------|
| Number of poles (control side) | 40-pole plug | Connection (field side) | LL2N 5.08 mm |
| Connection on control side | 2 x KS (40P) | | |

Ratings data

| | | | |
|-------------------|-------------------|--------------------------|-----|
| Operating voltage | 50 V AC / 70 V DC | Max. current per channel | 1 A |
|-------------------|-------------------|--------------------------|-----|

Insulation coordination (EN50178)

| | | | |
|----------------------------|-----------|-------------------------------|--------|
| Rated insulation voltage | < 50 V AC | Surge voltage category | III |
| Pollution severity level | 2 | Pulse voltage test (1,2/50µs) | 0.8 kV |
| Insulation test voltage AC | 0.35 kV | | |

Connection field

| | | | |
|----------------------------------|---------------------|----------------------------|---------------------|
| Min. wire cross-section, AWG | AWG 26 | Type of connection | Screw connection |
| Sleeve with plastic collar, max. | 2.5 mm ² | Flexible with sleeve, min. | 0.5 mm ² |
| Flexible with sleeve, max. | 2.5 mm ² | Flexible, max. H05(07) V-K | 4 mm ² |
| Flexible, min. H05(07) V-K | 0.5 mm ² | Solid, max. H05(07) V-U | 6 mm ² |
| Solid, min. H05(07) V-U | 0.5 mm ² | Stripping length | 6 mm |
| Tightening torque, max. | 0.6 Nm | Tightening torque, min. | 0.5 Nm |

TBY-C3-UNIV-SP-2KS-S

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

| | | | |
|------------------------------|-------------------|----------------------|----------------------|
| Clamping range, max. | 6 mm ² | Clamping range, min. | 0.13 mm ² |
| Max. wire cross-section, AWG | AWG 12 | | |

Supply connection

| | | | |
|------------------------------|---------------------|-----------------------------------|----------------------|
| Type of connection | Screw connection | Clamping range, min. | 0.13 mm ² |
| Clamping range, max. | 6 mm ² | Solid, min. H05(07) V-U | 0.5 mm ² |
| Solid, max. H05(07) V-U | 6 mm ² | Flexible, min. H05(07) V-K | 0.5 mm ² |
| Flexible, max. H05(07) V-K | 4 mm ² | Flexible with sleeve, max. | 2.5 mm ² |
| Flexible with sleeve, min. | 2.5 mm ² | Ferrule with plastic collar, max. | 0.5 mm ² |
| Wire cross-section, min. AWG | AWG 12 | Wire cross-section, max. AWG | AWG 26 |
| Tightening torque, min. | 0.5 Nm | Tightening torque, max. | 0.6 Nm |
| Stripping length | 6 mm | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002780 | ETIM 9.0 | EC002780 |
| ETIM 10.0 | EC002780 | ECLASS 14.0 | 27-14-11-52 |
| ECLASS 15.0 | 27-14-11-52 | | |