


KLIPPON COPL 082306

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

| | |
|------------|---|
| Version | Klippon POK (polyester empty enclosure), Earthing plate, Miscellaneous, Height: 33.5 mm, Width: 258 mm, Depth: 0.8 mm, Basic material: Brass, polished, untreated |
| Order No. | 1390950000 |
| Type | KLIPPON COPL 082306 |
| GTIN (EAN) | 4050118191301 |
| Qty. | 5 items |

KLIPPON COPL 082306

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|----------------------|---------|----------------------|--------------|
| Depth | 0.8 mm | Depth (inches) | 0.0315 inch |
| Height | 33.5 mm | Height (inches) | 1.3189 inch |
| Width | 258 mm | Width (inches) | 10.1575 inch |
| Wall thickness, min. | 0.8 mm | Wall thickness, max. | 0.8 mm |
| Net weight | 10.6 g | | |

Temperatures

| | |
|-----------------------|--|
| Operating temperature | |
|-----------------------|--|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General information

| | | | |
|--------------------|--------|----------------|---------------------|
| Material thickness | 0.8 mm | Surface finish | polished, untreated |
| Basic material | Brass | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002623 | ETIM 9.0 | EC002623 |
| ETIM 10.0 | EC002623 | ECLASS 14.0 | 27-18-28-14 |
| ECLASS 15.0 | 27-18-28-14 | | |