

VPU III 3/280V

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

There is a successor product



Type III surge protection

- Compact Type III arrester for AC/DC protection acc. to IEC 61643-11:2012
- Suitable for protecting terminals
- Installed in the vicinity of the equipment to be protected
- Can be used as single-port arrester when nominal current is greater than 16 A

General ordering data

Version	Surge voltage arrester, Low voltage, with remote contact, TN-C, TN-S, TN-C-S
Order No.	1393050000
Type	VPU III 3/280V
GTIN (EAN)	4050118193862
Qty.	1 items
Delivery status	Discontinued
Available until	2025-07-14T00:00:00+02:00
Alternative product	VPU AC II+III 3 R 275/20 S

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	57 mm	Depth (inches)	2.2441 inch
Height	90 mm	Height (inches)	3.5433 inch
Width	70 mm	Width (inches)	2.7559 inch
Net weight	164 g		

Temperatures

Storage temperature	-40 °C...70 °C	Operating temperature	-40 °C...70 °C
Humidity	5 - 95% rel. humidity		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Connection data, remote alert

Cross-section for connected wire, solid core, min.	0.2 mm ²	Stripping length	5 mm
Connection type	Screw connection	Cross-section for connected wire, solid core, max.	1.5 mm ²
Max. torque	0.22 Nm		

General data

Optical function display	Green LED = OK, Red LED = arrester is defective, replace	Segment	Power distribution
Version	with remote contact	Design	Installation housing; 1TE, Insta IP 20
UL 94 flammability rating	V-0	Colour	grey
Protection degree	IP20	Mounting rail	TS 35

Insulation coordination acc. to EN 50178

Surge voltage category	III	Pollution severity	2
------------------------	-----	--------------------	---

Rated data IEC / EN

Number of poles	1	Combined pulse UOC	6 kV
Leakage current at Un	30 µA	Signalling contact	250 V 10 A 1 NC
Rated voltage (AC)	230 V	Rated current IN	16 A
Low voltage network	TN-C, TN-S, TN-C-S	Mains frequency at 250 Vmax	50...60Hz
Protection level Up at IN (N-PE)	≤ 1400 V	Voltage type	3-phase 230/400 V
Temporary surge voltage (over-voltage) - TOV	440 V	Fuse protection	16 A

VPU III 3/280V

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Response time / fallback time	≤ 100 ns	Standards	IEC61643-11, EN61643-11
Requirements class, acc. to EN 61643-11	T3	Requirements category acc. to IEC 61643-11	Type III
Max. continuous voltage, U _c (AC)	275 V	Energy coordination (≤10 m)	Type II, Type III
Discharge current I _{max} (8/20μs) wire-PE3 kA		Protection level U _p at IN (L/N-PE)	≤ 1200 V
Short-circuit current rating ISCCR	1.5 kA	Discharge current (type III)	3 kA
Integrated back-up fuse	No	PE conductor current IPE	30 μA

Connection data

Stripping length	7 mm	Type of connection	Screw connection
Stripping length, rated connection	7 mm	Tightening torque, min.	0.4 Nm
Tightening torque, max.	0.5 Nm	Clamping range, rated connection	2.5 mm ²
Clamping range, min.	0.5 mm ²	Clamping range, max.	2.5 mm ²
Wire cross-section, solid, min.	0.5 mm ²	Wire cross-section, solid, max.	2.5 mm ²
Wire connection cross section, finely stranded, min.	0.5 mm ²	Wire connection cross section, finely stranded, max.	2.5 mm ²
Conductor cross-section, flexible, AEH (DIN 46228-1), min.	0.5 mm ²	Conductor cross-section, flexible, AEH (DIN 46228-1), max.	2.5 mm ²
Connection cross-section, stranded, min. 0.5 mm ²		Connection cross-section, stranded, max.	2.5 mm ²

Electrical data

Voltage type 3-phase 230/400 V

General data

Number of poles 1 Protection degree IP20
Colour grey

Guarantee

Time interval 5 years

Classifications

ETIM 8.0	EC000942	ETIM 9.0	EC000942
ETIM 10.0	EC000942	ECLASS 14.0	27-17-12-03
ECLASS 15.0	27-17-12-03		

Tender specification sheets


Long specification	Three-pin surge protection according to the requirements of Class III in accordance with IEC 61643-11, EN61643-11:2013. The arrester serves as surge protection and is used in applications in accordance with IEC 61643-12. The arrester is installed in a standard installation/distributor housing in the vicinity of the equipment that needs protection. The VPU III 3 280 V is earthed between the outer	Short specification	Class III arrester with U _{oc} : 6 kV suitable for 230/400 V TN-S mains systems. Protection level < 1.8 kV. With remote alert Type: Weidmüller VPU III 3 280 V Order no. 1393050000 or equivalent
--------------------	--	---------------------	--

Technical data

conductors (L1, L2, L3 and the neutral conductor).
With thermal separation device on the varistor.
If there is no longer any protection, the colour of the LEDs changes from green to red. The functional state is also displayed by a voltage-free signalling contact (NC contact). Rated voltage: 230 V AC I_n/max (8/20 µs):3 kA protection level < 1.8 kV load current II: 16A telecommunication output: contact NC: 250 V/0.5 A 48 V DC/0.1 A Type: Weidmüller VPU III 3 280 V Order No. 1393050000 or equivalent

Drawings

Electric symbol



Schematic circuit diagram

Accessories**Crosshead screwdriver Phillips**

VDE insulated crosshead screwdriver, for Phillips screws, SDIK PH DIN 7438, ISO 8764/2-PH, output to ISO 8764-PH, SoftFinish grip

General ordering data

Type	SDIK PH0 X 60	Version	
Order No.	2749880000	Screwdriver, Blade width (B): 0 mm, 60 mm, Blade thickness (A): 0	
GTIN (EAN)	4050118897081		
Qty.	1 ST		