

## CLI M 2-40Q NE MP

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



CLI M identification markers are slid onto CLI MH carrier strips and secured by means of cable ties. The system is particularly suitable for large conductor and cable cross-sections. Advantages:

- Combination marker for cable and pipe markers
- One size for all diameters above 16 mm<sup>2</sup>
- Unrestricted combination options
- Closed, permanently attached markers
- Very good legibility

### General ordering data

Version	CableLine, Conductor and cable markers, 10 - 317 mm, 4 x 11.4 mm
Order No.	<a href="#">1395680000</a>
Type	CLI M 2-40Q NE MP
GTIN (EAN)	4050118196115
Qty.	20 items

## CLI M 2-40Q NE MP

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	3 mm	Depth (inches)	0.1181 inch
Height	4 mm	Height (inches)	0.1575 inch
Width	11.4 mm	Width (inches)	0.4488 inch
Net weight	1.04 g		

## Temperatures

Operating temperature range	-30...80 °C
-----------------------------	-------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## General data

Number per sheet	20	
Type of printing	neutral	
Version	MultiPack	
Width	11.4 mm	
UL 94 flammability rating	V-0	
Operating temperature range, max.	80 °C	
Operating temperature range, min.	-30 °C	
Halogen	Yes	
Basic material	PVC, soft, without Cadmium	
Printed characters	neutral	
Number of markers per packaging unit	Form of supply	Component part
Recommended industries	Process, Machinery	
Number of markers per combination	1 Component part = Conductor and cable markers	
Operating temperature range	-30...80 °C	

## Conductor and cable markers

Halogen	Yes	Conductor cross-section, max.	500 mm <sup>2</sup>
Conductor cross-section, min.	16 mm <sup>2</sup>	Conductor O.D., max.	317 mm
Conductor O.D., min.	10 mm	Conductor O.D.	10 - 317 mm
Cross-section for connected wire	16 - 500 mm <sup>2</sup>		

## Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		