
### **KLIPPON COPL 121209**



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com







The Klippon® POK enclosure range is made from a highquality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- · Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

#### **General ordering data**

Version	Klippon POK (polyester empty enclosure), Earth- ing plate, Miscellaneous, Height: 57.5 mm, Width: 177 mm, Depth: 0.8 mm, Basic material: Brass, polished, untreated
Order No.	<u>1390970000</u>
Туре	KLIPPON COPL 121209
GTIN (EAN)	4050118191127
Qty.	5 items

Catalogue status / Drawings



## **KLIPPON COPL 121209**



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

Approvals				
ROHS	Conform			
Dimensions and weights	 S			
Depth	0.8 mm	Depth (inches)	0.0315 inch	
Height	57.5 mm	Height (inches)	2.2638 inch	
Width	177 mm	Width (inches)	6.9685 inch	
Wall thickness, min.	0.8 mm	Wall thickness, max.	0.8 mm	
Net weight	13 g			
Temperatures				
Operating temperature				
Environmental Product (	compliance			
RoHS Compliance Status		Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%			
General information				
Material thickness	0.8 mm	Surface finish	polished, untreated	
Basic material	Brass			
Classifications				
ETIM 6.0	EC002623	ETIM 7.0	EC002623	
ETIM 8.0	EC002623	ETIM 9.0	EC002623	
ETIM 10.0	EC002623	ECLASS 9.0	27-18-28-14	
ECLASS 9.1	27-18-92-64	ECLASS 10.0	27-18-28-14	
ECLASS 11.0	27-18-28-14	ECLASS 12.0	27-18-28-14	
ECLASS 13.0	27-18-28-14	ECLASS 14.0	27-18-28-14	
ECLASS 15.0	27-18-28-14			