


## KLIPPON COPL 122209

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Similar to illustration



The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

### General ordering data

Version	Klippon POK (polyester empty enclosure), Earthing plate, Miscellaneous, Height: 57.5 mm, Width: 275 mm, Depth: 0.8 mm, Basic material: Brass, polished, untreated
Order No.	<a href="#">1390980000</a>
Type	KLIPPON COPL 122209
GTIN (EAN)	4050118191080
Qty.	5 items

**KLIPPON COPL 122209**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	0.8 mm	Depth (inches)	0.0315 inch
Height	57.5 mm	Height (inches)	2.2638 inch
Width	275 mm	Width (inches)	10.8268 inch
Wall thickness, min.	0.8 mm	Wall thickness, max.	0.8 mm
Net weight	18.13 g		

**Temperatures**

Operating temperature

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General information**

Material thickness	0.8 mm	Surface finish	polished, untreated
Basic material	Brass		

**Classifications**

ETIM 8.0	EC002623	ETIM 9.0	EC002623
ETIM 10.0	EC002623	ECLASS 14.0	27-18-28-14
ECLASS 15.0	27-18-28-14		