


## KLIPPON COPL 256012

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

### Similar to illustration



The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

### General ordering data

|            |   |
|------------|---|
| Version    | Klippon POK (polyester empty enclosure), Earthing plate, Miscellaneous, Height: 85.5 mm, Width: 785 mm, Depth: 0.8 mm, Basic material: Brass, polished, untreated |
| Order No.  | <a href="#">1391050000</a>  |
| Type       | KLIPPON COPL 256012   |
| GTIN (EAN) | 4050118191233   |
| Qty.       | 5 items   |

**KLIPPON COPL 256012**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

|                      |         |                      |              |
|----------------------|---------|----------------------|--------------|
| Depth                | 0.8 mm  | Depth (inches)       | 0.0315 inch  |
| Height               | 85.5 mm | Height (inches)      | 3.3661 inch  |
| Width                | 785 mm  | Width (inches)       | 30.9054 inch |
| Wall thickness, min. | 0.8 mm  | Wall thickness, max. | 0.8 mm       |
| Net weight           | 89 g    |                      |              |

**Temperatures**

Operating temperature

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General information**

|                    |        |                |                     |
|--------------------|--------|----------------|---------------------|
| Material thickness | 0.8 mm | Surface finish | polished, untreated |
| Basic material     | Brass  |                |                     |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002623    | ETIM 9.0    | EC002623    |
| ETIM 10.0   | EC002623    | ECLASS 14.0 | 27-18-28-14 |
| ECLASS 15.0 | 27-18-28-14 |             |             |