

THM WO VIN 24.5/100 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Version	THM, Conductor and cable markers, 8 - 23 mm, 24.5 x 100 mm, white
Order No.	1391430000
Type	THM WO VIN 24.5/100 WS
GTIN (EAN)	4050118191714
Qty.	1 ROL

THM WO VIN 24.5/100 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	0.07 mm	Depth (inches)	0.0026 inch
Height	24.5 mm	Height (inches)	0.9646 inch
Width	100 mm	Width (inches)	3.937 inch
Net weight	994 g		

Temperatures

Operating temperature range -40...80 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Adhesive	Polyacrylate adhesive		
Type of printing	neutral		
Version	Self-adhesive		
Width	100 mm		
UL 94 flammability rating	V-0		
Operating temperature range, max.	80 °C		
Operating temperature range, min.	-40 °C		
Colour	white		
Halogen	Yes		
Basic material	Vinyl film		
Printed characters	without		
Number of markers per packaging unit	Form of supply	Label reel	
Size of labelling field	25 x 24.5 mm		
Approval acc. to UL 969	No		
compatible printer	THM MULTIMARK , THM MULTIMARK PLUS		
Number of markers per combination	1 Label reel = Conductor and cable markers		
Operating temperature range	-40...80 °C		
Number per roll	2000		

Conductor and cable markers

Halogen	Yes	Conductor cross-section, max.	95 mm ²
Conductor cross-section, min.	0.75 mm ²	Conductor O.D., max.	23 mm
Conductor O.D., min.	8 mm	Text field width	24.5 mm
Text field height	25 mm	Conductor O.D.	8 - 23 mm
Cross-section for connected wire	0.75 - 95 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

Drawings

