

HDC HP550 KIT 4F

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The RockStar® HighPower system, with its completely newly developed and coordinated components in three and four pin versions, represents a novel product solution for pluggable energy transmission – failure-free

The RockStar® HighPower system has a modular design and offers the customer a multitude of product solutions for all kinds of application sites and requirements.

The RockStar® HighPower end-wall connector is impact-resistant, water and dust-proof and was built to comply with DIN EN 61373 CAT 1b (bogie) requirements.

The overall structure has been adapted to the confined space of wagon-to-wagon coupling - small, light and powerful

General ordering data

Version	HDC kits, 1500 V, 550 A, Number of poles: 4, Screw connection
Order No.	1396250000
Type	HDC HP550 KIT 4F
GTIN (EAN)	4050118197631
Qty.	1 items

HDC HP550 KIT 4F

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	229 mm	Depth (inches)	9.0157 inch
Height	162 mm	Height (inches)	6.3779 inch
Width	260 mm	Width (inches)	10.2362 inch
Length	162 mm	Length (inches)	6.3779 inch
Net weight	7270 g		

Temperatures

Limit temperature	-40 °C ... 120 °C
-------------------	-------------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	a1b198df-2a58-40a5-bb31-ff1a2bb12993

Dimensions

Width	260 mm
-------	--------

General data

Number of poles	4	Type of connection	Screw connection
Design of housing	Base housing	UL 94 flammability rating	V-0
Colour	black (similar to RAL 9005)	Housing main material	diecast aluminium
Surface finish	Powder coating	Basic material	diecast aluminium
Series	HighPower	Rated voltage (DIN EN 61984)	1500 V
Rated impulse voltage (DIN EN 61984)	10 kV	Rated current (DIN EN 61984)	550 A
Free from halogens	false	Protection degree	IP68 when locked

General data

Connection type PE	Screw connection	Type of connection	Screw connection
Colour	black (similar to RAL 9005)	Surface finish	Powder coating
Enclosure material	Aluminium diecast	Basic material	diecast aluminium
Series	HighPower	Material of gasket	Silicone rubber
Material of contact	Copper alloy		

Important note

Product information	Depending on the intended operation, internally generated voltages can superimpose the working voltage and contain corresponding peaks. It is imperative to ensure that these peak voltages do not exceed the rated voltage. For applications outside of this specification, please contact us.
---------------------	---

Classifications

ETIM 8.0	EC002641	ETIM 9.0	EC002641
ETIM 10.0	EC002641	ECLASS 14.0	27-44-03-06

ECLASS 15.0

27-44-03-06
